



Heyco® Original Strain Relief Bushings

Right Angle for Round Cables


- Provides the same protection for your power supply cable as the straight-thru type AND...
- **Exits the cable flush against the panel**, saving space and directing the cable parallel to the panel.
- Overcomes space limitations and acts as a back or bottom bumper.
- See page 4-38 for corresponding **Mounting Hole Plugs** which can be used to fill blank/unused Mounting Holes and thus allow for a single panel design for multiple applications.
- Consult Heyco for other wire types and sizes.
- See pages 4-27 & 4-28 for SR assembly tools.
- For Double D Mounting Hole Punches, see page 4-30.

WILL FIT THESE CABLES				PANEL DIMENSIONS						PART NO. Black	DESC.	PART DIMENSIONS				Mounting
UL Type	AWG/ Conductors	Approximate Size		A Mounting Hole Dia.		B To Prevent Rotation		Finished Fit Panel Thickness*				C HEAD LENGTH	D BODY LENGTH		Hole Plug	
		in.	mm.	in.	mm.	in.	mm.	in.	mm.			in.	mm.	in.	mm.	PART NO.
SV & SVT	18/2	.250	6,4	.500	12,7	.450	11,4	.100	2,5	1374	SR 15-1	.39	9,9	.69	17,5	2491
	18/3	.265	6,7	.500-.515	12,7-13,1											
HPD	18/2	.270	6,9	.500	12,7	.450	11,4	.100	2,5	1374	SR 15-1	.39	9,9	.69	17,5	2491
	16/2	.290	7,4	.500-.515	12,7-13,1											
SJ, SJO & SJT	18/2	.300	7,6	.625	15,9	.550	14,0	.125	3,2	1320	SR 10-2	.56	14,3	.97	24,6	2497
	16/2	.325	8,3													
	18/3	.330	8,4													
SJ	16/3	.330	8,4	.625	15,9	.550	14,0	.125	3,2	1327	SR 11-2	.56	14,3	.97	24,6	2497
SJ, SJO & SJT	16/2	.325	8,3													
	18/3	.330	8,4													
	16/3	.335	9,0													
SJT	18/4	.360	9,1	.750	19,0	.660	16,8	.125	3,2	1397	SR 17-2	.64	16,3	1,09	27,7	2503
SJT & SJTO	14/3	.370	9,4													
SJ & ST	18/2	.390	9,9													
	18/3	.405	10,3													
	16/2	.405	10,3													
S	16/3	.430	10,9	.750-.781	19,0-19,8	.660	16,8	.125	3,2	1397	SR 17-2	.64	16,3	1,09	27,7	2503
	14/2	.530	13,5													
S	14/3	.560	14,2	.875	22,2	.815	20,7	.125	3,2	1401	SR 18-2	.84	21,4	1,36	34,5	2509
	14/3	.560	14,2													


NEW!

Standard color black. Consult Heyco for white and other colors.

*Maximum Panel Thickness. Part has additional clearance. Consult Heyco for your Custom Finished Fit Panel Thickness.



MOUNTING HOLES



Quick Specs

Material
Certifications

Nylon 6/6



Recognized under the Component Program of Underwriters' Laboratories File E15331



Certified by the Canadian Standards Association File 8919

Flammability Rating
Temperature Range

94V-2

-.04°F (-18°C) to 221°F (105°C)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[1397](#) [1320](#) [1327](#) [1375](#) [1327FR](#) [1374GF](#) [1398](#) [1399](#) [1402](#) [1401](#) [1320-P](#)