




HEYClip™ RevRunner® Cable Clips for 1-2 Cables

Double-Compression, Straight-thru Design

PANEL THICKNESS CLAMPING RANGE				WIRE DIA. RANGE	PART NO.		DESCRIPTION	FOOTPRINT		OVERALL HEIGHT	
Minimum		Maximum			304	316		A x B		C	
in.	mm.	in.	mm.		Stainless	Stainless		in.	mm.	in.	mm.
RevRunner Clip - for panels up to .120" (3,0 mm) thick											
.06	1,4	.13	3,2	.20" (5,1 mm)- .33" (8,3 mm) each cable	S6507	–	RevRunner Clip 100 Pack	1.00 x .50	25,4 x 12,7	.39	9,9
					S6547	–	RevRunner Clip Bulk				

- Design is similar to the original SunRunner, but oriented so that cables are hidden inside the PV module frame for an aesthetically pleasing installation.
- Can hold 1 or 2 cables from .20" (5,1 mm) to .33" (8,3 mm).
- Installs on PV module frames or other areas with materials that are from .06" (1,4 mm) to .13" (3,2 mm) thick.



Material .025" thick 304 stainless steel
Temperature Range -40°F (-40°C) to 572°F (300°C)

*Quick
Specs*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[S6507](#) [S6547](#)