





Heyco® Screw to Tab Terminal Blocks

Screw to (3) Tabs Flame Retardant and UL 94V-0


WIRE SIZE AWG	mm ²	AMPS	POLES	PART NO. White	DESCRIPTION	Screws (Metric)	PART DIMENSIONS											
							A		B		C		D		E		F	
							in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.
8-18	10	40	3	9450	ATB-3P FR	M5,0	3.19	81,0	.59	15,0	1.00	25,4	2.60	66,0	.41	10,4	1.48	37,5
				9451	ATB-3P FR w/ Ground													
8-18	10	40	4	9452	ATB-4P FR	M5,0	3.90	99,0	.59	15,0	1.00	25,4	3.31	84,0	.41	10,4	1.48	37,5
8-18	10	40	6	9454*	ATB-6P FR	M5,0	5.31	135,0	.59	15,0	1.00	25,4	4.72	120,0	.41	10,4	1.48	37,5
				9455*	ATB-6P FR w/ Ground													
				9456	Jumper for Screw to Tab Poles													
				9457	Ground for Screw to Tab TB													

Standard color flame retardant white.

*Includes three jumpers. To order additional jumpers, see part 9456.



9457
GROUND CONTACT



9456
JUMPER

- Three .250" by .031" (6,3 by 0,8 mm) tabs per pole.
- ATB-3P poles are marked 1, 2, and .
- ATB-4P poles are marked 1, 2, 3 and .
- ATB-6P poles are marked 1, 2, 3, 4, 5 and .
- All sizes are rated at 300 volts.
- Self-grounding version is available. Identical to the base parts except that an extension on the grounding pole makes direct contact with the panel. The extension is secured with two self-tapping screws.
- Ground contact (**Part No. 9457**)—Grounds terminal block to the panel. May be ordered separately or with the listed Appliance Terminal Blocks.
- Jumper (**Part No. 9456**)—To connect terminal block poles. For use with Heyco's Screw to Tab terminal blocks.
- DFARS Compliant

Materials
Certifications

6/6 Nylon and galvanized steel
 Recognized under Component Program of Underwriters' Laboratories to both Canadian and US requirements File E197025

Flammability Rating
Temperature Range

94V-0
-4°F (-18°C) TO 302°F (150°C)

*Quick
Specs*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[9450](#) [9451](#) [9456](#) [9457](#) [9455](#) [9452](#)