




Heyco® Shorty Bushings

Single Locking Step for Panel Thickness up to .062" (1,6 mm)

Mounting Hole Diameter Range: .187" (4,7 mm) to 1.093" (27,8 mm)

MOUNTING HOLE DIAMETER		PART NO.		DESCRIPTION	PART DIMENSIONS					
in.	mm.	Black	White		A Inside Diameter		B Head Diameter		C Overall Height	
					in.	mm.	in.	mm.	in.	mm.
.187	4,7	2800	2801	B 187-125	.13	3,2	.25	6,4	.24	6,0
.218	5,5	2859	2860	B 218-125	.13	3,2	.28	7,1		
.281	7,1	2853	2854	B 281-218	.22	5,5	.34	8,7		
.307	7,8	2808	2809	B 307-244	.24	6,2	.38	9,7		
.312	7,9	2810	2811	B 312-250	.25	6,3	.38	9,7		
.343	8,7	2856	2857	B 343-218	.22	5,5	.41	10,3	.25	6,4
.375	9,5	2803	2804	B 375-250	.25	6,3	.44	11,1		
.390	9,9	2815	2816	B 390-265	.27	6,7	.43	10,9		
.406	10,3	2806	2807	B 406-281	.28	7,1	.47	11,9		
.437	11,1	2813	2814	B 437-312	.31	7,9	.50	12,7		
.468	11,9	2817	2818	B 468-343	.34	8,6	.53	13,5		
.500	12,7	2820	2821	B 500-375	.38	9,5	.56	14,3		
.512	13,0	2822	2823	B 512-375						
.531	13,5	2824	2825	B 531-406	.41	10,3	.59	15,1		
.593	15,1	2833	2834	B 593-468	.47	11,9	.66	16,7		
.625	15,9	2827	2828	B 625-500	.50	12,7	.70	17,9		
.687	17,4	2832	2835	B 687-562	.57	14,4	.76	19,3		
.750	19,1	2836	2837	B 750-625	.63	15,9	.83	21,0		
.781	19,8	2844	2845	B 781-625	.63	15,9	.86	21,8		
.875	22,2	2850	2851	B 875-750	.75	19,0	.95	24,0		
1.000	25,4	2847	2848	B 1000-875	.88	22,3	1.06	27,0		
1.093	27,8	2838	2839	B 1093-969	.97	24,6	1.16	29,4	.26	6,5

Standard colors black and white. Consult Heyco for other colors.



**SINGLE PANEL DESIGN
(PANEL MAY BE THINNER)**

Material
Certifications

Nylon 6/6



Recognized under the Component Program of Underwriters' Laboratories, File E15331



Certified by Canadian Standards Association, File 8919

Flammability Rating
Temperature Range

94V-2

-4°F (-18°C) to 221°F (105°C)

*Quick
Specs*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[2800](#) [2803](#) [2840](#) [2824](#) [2820](#) [2827](#) [2850](#) [2810](#) [2836](#) [2838](#) [2806](#) [2844](#) [2853](#) [2817](#) [2813](#) [2801](#) [2831](#) [2847](#)
[2821](#) [2833](#) [2814](#) [2825](#) [2807](#) [2854](#) [2818](#) [2837](#) [2856](#) [2848](#) [2859](#) [2804](#) [2811](#) [2841](#) [2860](#) [2828](#) [2839](#) [2857](#)
[2851](#) [2845](#) [2834](#) [2822](#) [2832](#) [2823](#) [2816](#) [2835](#) [2808](#) [2809](#) [2815](#) [2826](#) [2829](#) [2852](#)