



Heyco® -Tite UL Listed/Recognized and CSA Certified Liquid Tight Cordgrips for Solar Applications

Multi-Hole, NPT Hubs with Integral Sealing Ring - IP 68 Rated

The Ultimate in Liquid Tight Strain Relief Protection

- Integral Sealing Ring ensures a superior seal at the clearance or threaded mounting hole location, every time.
- IP 68 rated.
- Widest range of approved cable diameters.
- Cordgrips with an -SM suffix have Skinned-Over Break-thru glands that offer the flexibility to use from 1 to 31 of the available holes while still providing a liquid tight seal around the wire.
- All accompanying Cordgrips are made of nylon construction with TPE sealing glands that resist salt water, weak acids, gasoline, alcohol, oil, grease, and common solvents. (This feature is not assessed by UL.)
- For locknut specifications or to order locknuts separately, see pages 3-47 & 3-48.
- Multi-hole glands are only to be used with Heyco Liquid Tight Cordgrips and are not sold separately.
- For our complete range of Heyco Cordgrips, see Section 3.

GLAND CONFIGURATION		PART NUMBER	DESCRIPTION	UL/CSA or cRUUS	PART DIMENSIONS									
Size	Conductors				A	B	C	D	E					
mm.	No.	Black			Clearance Hole Dia.	Max. O.A. Length	Thread Length	Wrenching Thickness	Nut Flat Size					
					in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.
Standard Multi-Hole Gland - Assembled Metal Locknuts INCLUDED														
4,5	9	M8437GBF	LTCG 1	UL/CSA	1.326	33,8	2.41	61,2	.76	19,3	.30	7,6	1.73	43,9
	13	M4524GBG	LTCG 1-1/4	cRUUS	1.680	42,7	2.69	68,3	.78	19,8	.30	7,6	2.05	52,1
5,2	2	M3231GAE	LTCG 1/2	UL/CSA	.875	22,2	1.70	43,2	.61	15,5	.21	5,3	.98	24,9
	3	M3234GAF	LTCG 3/4	UL/CSA	1.109	28,2	2.00	50,8	.62	15,7	.25	6,4	1.30	33,0
	4	M3234GAG	LTCG 3/4	UL/CSA	1.109	28,2	2.00	50,8	.62	15,7	.25	6,4	1.30	33,0
5,6	3	M3200GAH	LTCG LL 1/2	UL/CSA	.875	22,2	1.68	42,7	.44	11,2	.25	6,4	1.06	27,0
Skinned-Over Break-thru Solar Masthead Gland - Assembled Metal Locknuts INCLUDED														
5,5	5	M3234GBR-SM	SMCG 3/4	cRUUS	1.109	28,2	2.00	50,8	.62	15,7	.25	6,4	1.30	33,0
	9	M8437GBK-SM	SMCG 1	cRUUS	1.326	33,8	2.41	61,2	.76	19,3	.30	7,6	1.73	43,9
	13	M4524GBM-SM	SMCG 1-1/4	cRUUS	1.680	42,7	2.69	68,3	.78	19,8	.30	7,6	2.05	52,1
	21	M3317GBQ-SM	SMCG 1-1/2	cRUUS	1.920	48,8	2.81	71,4	.76	19,3	.36	9,1	2.48	63,0
	31	M3321GBY-SM	SMCG 2	cRUUS	2.400	60,8	2.92	74,2	.79	20,1	.42	10,7	2.73	69,3
5,6	3	M3200GAH-SM	SMCG LL 1/2	UL/CSA	.875	22,2	1.68	42,7	.44	11,2	.25	6,4	1.06	27,0
7,7	3	M3234GBS-SM	SMCG 3/4	UL/CSA	1.109	28,2	2.00	50,8	.62	15,7	.25	6,4	1.30	33,0
	5	M8437GBT-SM	SMCG 1	UL/CSA	1.326	33,8	2.41	61,2	.76	19,3	.30	7,6	1.73	43,9
	9	M4524GBW-SM	SMCG 1-1/4	UL/CSA	1.680	42,7	2.69	68,3	.78	19,8	.30	7,6	2.05	52,1
	11	M3317GBZ-SM	SMCG 1-1/2	cRUUS	1.920	48,8	2.81	71,4	.76	19,3	.36	9,1	2.48	63,0
	19	M3321GBX-SM	SMCG 2	UL/CSA	2.400	60,8	2.92	74,2	.79	20,1	.42	10,7	2.73	69,3
8,9	7	M4524GCJ-SM	SMCG 1-1/4	UL/CSA	1.680	42,7	2.69	68,3	.78	19,8	.30	7,6	2.05	52,1
	9	M3317GCK-SM	SMCG 1-1/2	cRUUS	1.920	48,8	2.81	71,3	.76	19,3	.36	9,1	2.48	63,0
	12	M3321GCM-SM	SMCG 2	UL/CSA	2.400	60,8	2.93	74,3	.79	20,1	.42	10,7	2.75	69,9
Other Configurations with Approval Potential - Locknuts not included														
6,0	2	M3200GAJ	LTCG LL 1/2	-	.875	22,2	1.68	42,7	.44	11,2	.25	6,4	1.06	27,0
	4	M3234GBC	LTCG 3/4	-	1.109	28,2	2.00	50,8	.62	15,7	.25	6,4	1.30	33,0
6,5	6	M8437GAL	LTCG 1	-	1.326	33,8	2.41	61,2	.76	19,3	.30	7,6	1.73	43,9
		M4524GAL	LTCG 1-1/4	-	1.680	42,7	2.69	68,3	.78	19,8	.30	7,6	2.05	52,1
7,0	3	M3234GAM	LTCG 3/4	-	1.109	28,2	2.00	50,8	.62	15,7	.25	6,4	1.30	33,0
7,4	2	M3234GAN	LTCG 3/4	-	1.109	28,2	2.00	50,8	.62	15,7	.25	6,4	1.30	33,0



Use Heyco Multi-Hole Cordgrips with Heyco Female Threaded Couplings and Heyco-Flex III Tubing to insulate exposed PV wiring when making complete liquid tight connections to solar combiner or inverter enclosures. **See page 2-1 for details.**

Quick Specs

Material	Nylon 6/6 with TPE sealing gland
Certifications	- UL Listed under Underwriters' Laboratories File E51579 - cRUUS Recognized under the Component Program of Underwriters' Laboratories File E51579 to both Canadian and U.S. requirements - CSA Certified by the Canadian Standards Association File 93876
Flammability Rating	94V-2
Temperature Range	Static -40°F (-40°C) to 239°F (112°C) Dynamic -4°F (-20°C) to 212°F (100°C)
IP Rating	IP 68

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[M4524GBM-SM](#) [M8437GBK-SM](#) [M3317GBQ-SM](#) [M3321GBX-SM](#) [M3321GBY-SM](#) [M3200GAH-SM](#) [M3234GBS-](#)
[SM](#) [M4524GBW-SM](#) [M8437GBT-SM](#) [M4524GCJ-SM](#) [M3317GCK-SM](#) [M3321GCM-SM](#) [M3317GBZ-SM](#)
[M8437GCC-SM](#) [M3200GCQ-SM](#)