

"Stay Connected" with

HEYCO®

Solar Power Components

a PennEngineering® Company

Heyco®-Tite Solar Masthead® Metal Liquid Tight Cordgrips

Multi-Hole, NPT Hubs - IP 68 Rated



The Ultimate in Liquid Tight Strain Relief Protection

ALL NEW
PRODUCT!



GLAND CONFIGURATION Conductors Size mm.		PART NO.	DESCRIPTION	PACKAGING Standard Pack	 or 	A Clearance Hole Dia.		B Max. O.A. Length		C Thread Length		D Wrenching Nut Thickness		E Flat Size	
	No.					in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.
Stainless Steel															
5,5	9	M6013GBK-SM	SSMCG 1	25		1.375	34,9	2.22	56,4	.69	17,5	.20	5,1	1.75	44,5
	13	M6016GBM-SM	SSMCG 1-1/4	10		1.734	44,0	2.61	65,0	.71	18,0	.25	6,4	2.25	57,2
	21	M6018GBQ-SM	SSMCG 1-1/2	5		1.984	50,4	2.69	67,1	.73	18,5	.25	6,4	2.50	63,5
	31	M6020GBY-SM	SSMCG 2	5		2.469	62,7	2.92	74,2	.76	19,3	.25	6,4	2.75	69,9
7,7	5	M6013GBT-SM	SSMCG 1	25		1.375	34,9	2.22	56,4	.69	17,5	.20	5,1	1.75	44,5
	9	M6016GBW-SM	SSMCG 1-1/4	10		1.734	44,0	2.61	65,0	.71	18,0	.25	6,4	2.25	57,2
	11	M6018GBZ-SM	SSMCG 1-1/2	5		1.984	50,4	2.69	67,1	.73	18,5	.25	6,4	2.50	63,5
	19	M6020GBX-SM	SSMCG 2	5		2.469	62,7	2.92	74,2	.76	19,3	.25	6,4	2.75	69,9
8,9	7	M6016GCJ-SM	SSMCG 1-1/4	10		1.734	44,0	2.61	65,0	.71	18,0	.25	6,4	2.25	57,2
	9	M6018GCK-SM	SSMCG 1-1/2	5		1.984	50,4	2.69	67,1	.73	18,5	.25	6,4	2.50	63,5
	12	M6020GCM-SM	SSMCG 2	5		2.469	62,7	2.92	74,2	.76	19,3	.25	6,4	2.75	69,9

Assembled Metal Locknuts INCLUDED.



- Break-Thru Skinned-Over glands offer flexibility to use from 1 to 31 of the available holes while still providing a liquid tight seal around the wire.
- Rolled grease-free threads prevent galling and allow for multiple assemblies and disassemblies.
- Approved for NEMA 4, 4X, 6 and 6P applications.
- Self-retaining sealing washers eliminate the need for an O-Ring groove, thus reducing cost.
- Stainless Steel ideal for corrosive environments.
- Provide a watertight seal for PV module output leads to inverters.
- Secure input PV leads from solar panel array strings to fuse holder hookup within solar combiner boxes.
- No disassembly required for installation.
- Sealing washer required for through hole applications only.
- DFARS Compliant.

Material	SSMCG: 303 Stainless Body and sealing nut with Nylon 6/6 finger and TPE Gland
Certifications	 Certified by UL for Compliance with both Canadian and US requirements under File E51579  Recognized under the Component Program of Underwriters' Laboratories File E51579 to both Canadian and US requirements
Flammability Rating	94V-2
Temperature Range	-40°F (-40°C) to 212°F (100°C)
IP Rating	IP 68 (70 PSI, 5 BAR)

Quick
Specs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[M6113GBT-SM](#) [M6116GBW-SM](#) [M6113GBK-SM](#) [M6118GBZ-SM](#) [M6020GDF-SM](#) [M6018GDG-SM](#) [M6016GDH-SM](#)