



Heyco® Strain Relief Mounting Hole Plugs

Multiple Panel Thickness Design





PANEL DIMENSIONS						PART NO.	DESCRIPTION	PART DIMENSIONS			
Maximum Thickness		D Mounting Hole Diameter		C To Prevent Rotation				A Head Diameter		B Overall Height	
in.	mm.	in.	mm.	in.	mm.	Black		in.	mm.	in.	mm.
For Double D Mounting Hole Strain Reliefs											
.125	3,2	.375	9,5	.345	8,8	2617	DP 375*	.468	11,9	.406	10,3
		.437	11,1	.390	9,9	2488	DD 437-390	.531	13,5		
		.500	12,7	.445	11,3	2491	DD 500-445	.554	14,7		
.125	3,2	.562	14,3	.530	13,5	2494	DD 562-530	.656	16,7	.406	10,3
		.625	15,9	.550	14,0	2497	DD 625-550	.728	18,5		
		.750	19,1	.625	15,9	2503	DD 750-625	.921	23,4		
.125	3,2	.875	22,2	.770	19,5	2509	DD 875-770	1.016	25,8	.453	11,5
		1.109	28,2	1.000	25,4	2717	DD 1109-1000	1.218	30,9		
.125	3,2	2.000	50,8	1.875	47,6	2959	DD 2000-1875	2.170	55,1	.478	12,1
For Lockit ST-Series, Rectangular Mounting Hole Strain Reliefs**											
.099	2,5	.512	13,0	.453	11,5	1890†	RP 115-130	.580	14,7	.403	10,2
.157	4,0	.690	17,5	.690	17,5	1892	RP 175-175	.830	21,1	.470	11,9

Standard color black. Consult Heyco for white and other colors.

*On installation, DP 375 Locking Fingers must be aligned with Mounting Hole Flats.

**Rectangular Plugs locking finger steps match those of the corresponding ST Lockit Strain Reliefs.

†PN 1890 is not CSA certified.



PART NUMBERS 1890/1891

1890, 1892

Material

Nylon 6/6

Certifications



Recognized under the Component Program of Underwriters' Laboratories
File E51579



Certified by the Canadian Standards Association File 8919

Flammability Rating

94V-2

Temperature Range

-40°F (-40°C) to 221°F (105°C)

*Quick
Specs*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[2497](#) [2488](#) [2509](#) [2717](#) [2503](#) [2963](#) [2959](#) [1890](#) [1892](#) [2512](#) [2546](#) [2511](#) [2492](#) [2504](#) [2510](#) [2718](#) [2498](#) [2495](#)
[2489](#) [3299](#) [1892CB](#)