



Heyco® Universal Bushings

Mounting Hole Diameter Range: .500" (12,7 mm) to 3.000" (76,2 mm)

- Flexible shutters adjust to accommodate and support **any shape** from .125" (3,2 mm) to a maximum cable/bundle diameter of 2.470" (62,7 mm).
- Absorb vibration and cushion and insulate cables, tubing, hoses or shafts.
- Locking fingers in fractional increments up to the maximum panel thickness.
- Fingertip pressure snap-locks the bushing into its mounting hole.

MOUNTING HOLE DIAMETER		PART NO.		DESCRIPTION	PART DIMENSIONS					
in.	mm.	Black	White		Maximum Cable/ Bundle Diameter		A Head Diameter		B Overall Height	
					in.	mm.	in.	mm.	in.	mm.

Multiple Locking Steps for Panel Thickness up to .125" (3,2 mm)



.500	12,7	2055	2056	UB 500	.31	7,6	.60	15,2	.39	9,8
.625	15,9	2077	2076	UB 625	.44	11,1	.73	18,5	.41	10,3
.750	19,1	2089	2085	UB 750	.50	12,7	.84	21,4		
.812	20,6	2106	2107	UB 812	.50	12,7	.89	22,6	.39	9,9
.875	22,2	2119	2129	UB 875	.56	14,3	.94	23,8	.45	11,5
		2118	—	UB 875-112*						
1.000	25,4	2137	2138	UB 1000	.75	19,1	1.06	27,0	.44	11,2
1.093	27,8	2157	2162	UB 1093	.81	20,6	1.16	29,5		
1.187	30,2	2153	2154	UB 1187	.95	24,1	1.25	31,8		
1.250	31,8	2155	2156	UB 1250	1.02	25,8	1.31	33,4	.45	11,5
1.375	34,9	2184	2185	UB 1375	1.00	25,4	1.49	37,8		
		2187	—	UB 1375-1750	1.00	25,4	1.75	44,5		
1.500	38,1	2213	2214	UB 1500	1.06	26,9	1.61	40,9		
1.750	44,5	2298	2299	UB 1750	1.38	34,9	1.87	47,5	.47	11,8
2.000	50,8	2422	2423	UB 2000	1.64	41,6	2.13	54,0	.49	12,4

Multiple Locking Steps for Panel Thickness up to .250" (6,4 mm)

2.500	63,5	2440	2441	UB 2.500	1.97	50,0	2.63	66,8	.75	19,05
3.000	76,2	2460	2463	UB 3.000	2.47	62,7	3.15	80,0		

Standard colors black and white. Consult Heyco for other colors.

*UB 875-112 inside diameter adjusts for 1/8" to 5/8" cables; UB 875 adjusts for 3/16" to 9/16" cables.



*Quick
Specs*

Material
Certifications

Nylon 6/6

UL Recognized under the Component Program of Underwriters' Laboratories, File E15331

CSA Certified by Canadian Standards Association, File 8919

Flammability Rating
Temperature Range

94V-2

-4°F (-18°C) to 221°F (105°C)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[2108](#) [2213PP](#) [2119CL](#) [2129CJ](#) [2055-P](#) [2153-P](#) [2184-P](#) [2213-P](#) [2298-P](#) [2422-P](#) [2440-P](#) [2460-P](#)