







RECOMMENDED LAND PATTERN DIMENSION OF PCB
RECOMMENDED METAL MASK THICKNESS:0.15mm)



SIGNAL PORTION CROSS SECTION (10:1)



GROUND PORTION CROSS SECTION (10:1)




- NOTES
- ① 6 HATCHED  PARTS: GROUND CIRCUIT.
 - 2 SMT LEAD-COPLANARITY: 0.1 MAX.
 - 3 THIS PRODUCT HAS NO POLARITY TO PATTERN FOR MOUNTING.
 - ④ MAKE SURE WIDTH OF PATTERN IS WITHIN THAT OF LAND, OR LEAD MAY TOUCH PATTERN. (THIS APPLIES TO HATCHED  AREA.)
 - ⑤ DO NOT MOUNT OTHER DEVICES ONTO   AREA, OR MATING PAIR CANNOT BE MATED.
 - 6 TO BE EMBOSSED CARRIER TAPED AS SPECIFIED IN SHEET 2.
 - 7 THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

3, 4	PHOSPHOR BRONZE	TIN PLATING			
2	COPPER ALLOY	CONTACT AREA : GOLD 0.1μm min.			
		LEAD AREA : GOLD FLASH	7	POLYIMIDE	(TAPE FOR VACUUM PICKUP)
		UNDER PLATING : NICKEL 1μm min.	6	PET	TOP COVER TAPE
1	LCP	BEIGE UL94V-0	5	PS	EMBOSSSED CARRIER TAPE
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS

UNITS mm		SCALE 5 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.		APPROVED : HS. OKAWA		13. 08. 07	DRAWING NO.	EDC3-152601-02		
		CHECED : HT. YAMAGUCHI		13. 08. 07	PART NO.	FX11B-60P/6-SV(92)		
		DESIGNED : TY. EDAGAWA		13. 08. 07	CODE NO.	CL573-0512-3-92		
		DRAWN : TY. EDAGAWA		13. 08. 07				





DRAWING FOR PACKING(2:1)




THE DIRECTION OF PULLING OUT →


A (5:1)



DETAIL FOR VACUUM PICKUP (5:1)



REELED DIMENSION(Free)



- NOTES
- 1 REEL : 1000 CONNECTORS.
 - 2 MINIMUM 10 COMPARTMENTS FROM BOTH REEL ENDS REMAIN EMPTY.
 - 3 THIS PRODUCT HAS NO POLARITY TO TAPE AND REEL PACKAGING.
 - 4 THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.
 - 5 REMOVE THE VACUUM PICKUP TAPE AFTER MOUNTING THE CONNECTOR.

HRS

DRAWING NO.	EDC3-152601-02
PART NO.	FX11B-60P/6-SV(92)
CODE NO.	CL573-0512-3-92

2/2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[FX11B-60P/6-SV\(92\)](#)