




NOTE 1. LEAD CO-PLANALITY INCLUDE REINFORCED METAL FITTING SHALL BE 0.1 MAX.
2. WHEN THIS CONNECTOR MATES WITH DF14-S-1.25C, THE MATTING LENGTH IS 7.3mm.
3. FOR CONNECTORS, 2 OR 3 CONTACTS, SIMPLIFIED LOCK HOLE SHALL BE SET AT THE CENTER OF HOUSING.

3	PHOSPHOR BRONZE	TIN-COPPER PLATED 1μm min UNDER PLATING-NICKEL PLATED 0.5μm min
2	BRASS	TIN-COPPER PLATED 1μm min UNDER PLATING-NICKEL PLATED 0.5μm min
1	POLYAMIDE	BEIGE, UL94V-0
NO.	MATERIAL	FINISH, REMARKS
CODE NO. (OLD)	CL	

DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
F. Matsuki	S. Sankawa	T. Miyagaki	T. Miyagaki	
03.3.5	03.3.7	03.03.25	03.03.25	

DRAWING NO.	PART NO.
EDC3-160307-19	DF14-S-P-1.25H(26)
SCALE 5 : 1	CODE NO.
UNITS mm	CL538-

HRS



HIROSE ELECTRIC CO., LTD

CL538-

1/2

COUNT		DESCRIPTION OF REVISIONS	BY	CHKD	DATE	DESCRIPTION OF REVISIONS		BY	CHKD	DATE
△						△				
△						△				
△						△				

PART NO.	CONTACTS	G	H	J	K	M
DF14- 2P-1.25H(26)	2	7.5	-	16	7.85	16.4
DF14- 3P-1.25H(26)	3	7.5	-	16	9.1	16.4
DF14- 4P-1.25H(26)	4	11.5	-	24	10.35	24.4
DF14- 5P-1.25H(26)	5	11.5	-	24	11.6	24.4
DF14- 6P-1.25H(26)	6	11.5	-	24	12.85	24.4
DF14- 7P-1.25H(26)	7	11.5	-	24	14.1	24.4
DF14- 8P-1.25H(26)	8	11.5	-	24	15.35	24.4
DF14- 9P-1.25H(26)	9	11.5	-	24	16.6	24.4
DF14- 10P-1.25H(26)	10	11.5	-	24	17.85	24.4
DF14- 15P-1.25H(26)	15	20.2	40.4	44	24.1	44.4
DF14- 20P-1.25H(26)	20	20.2	40.4	44	30.35	44.4
DF14- 25P-1.25H(26)	25	26.2	52.4	56	36.6	56.4
DF14- 30P-1.25H(26)	30	26.2	52.4	56	42.85	56.4

[illegible]

生産月日	年 月 日
CLコード	538-*****-26
品名	DF14-*P-1.25H(26)
納入数量	1000個
納入者	ヒロセ電機株式会社

NOTES 4 1 REEL : 1000 CONNECTORS.

5 AT THE BEGINNING OF THE REEL, 30 COMPONENTS SHALL BE EMPTY.

6>AT THE END OF THE REEL , 20 COMPONENTS SHALL BE EMPTY.

WHEN THE TAPE WIDTH IS 44 TO 56mm , SPROCKET HOLES SHALL

BE SET ON BOTH SIDES OF REEL AS SHOWN ON THIS DRAWING.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[DF14-3P-1.25H\(26\)](#)