







5					6					7					8				
COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△				.	△				.	△				.	△				.
△				.	△				.	△				.	△				.
△				.	△				.	△				.	△				.



PART NO.		HRS NO.	CONTACTS	A	B	C	D	E
DF14A-	2P-1.25H(56)	CL538-0033-3-56	2	7.45	1.25	2.95	3.65	8.05
DF14A-	3P-1.25H(56)	CL538-0034-6-56	3	8.70	2.50	4.20	4.90	9.30
DF14A-	4P-1.25H(56)	CL538-0035-9-56	4	9.95	3.75	5.45	6.15	10.55
DF14A-	5P-1.25H(56)	CL538-0036-1-56	5	11.20	5.00	6.70	7.40	11.80
DF14A-	6P-1.25H(56)	CL538-0037-4-56	6	12.45	6.25	7.95	8.65	13.05
DF14A-	7P-1.25H(56)	CL538-0038-7-56	7	13.70	7.50	9.20	9.90	14.30
DF14A-	8P-1.25H(56)	CL538-0039-0-56	8	14.95	8.75	10.45	11.15	15.55
DF14A-	9P-1.25H(56)	CL538-0040-9-56	9	16.20	10.00	11.70	12.40	16.80
DF14A-	10P-1.25H(56)	CL538-0041-1-56	10	17.45	11.25	12.95	13.65	18.05
DF14A-	15P-1.25H(56)	CL538-0114-3-56	15	23.70	17.50	19.20	19.90	24.30
DF14A-	20P-1.25H(56)	CL538-0119-7-56	20	29.95	23.75	25.45	26.15	30.55
DF14A-	25P-1.25H(56)	CL538-0124-7-56	25	36.20	30.00	31.70	32.40	36.80
DF14A-	30P-1.25H(56)	CL538-0045-2-56	30	42.45	36.25	37.95	38.65	43.05




NOTE 1. LEAD CO-PLANALITY INCLUDE REINFORCED METAL FITTINGS SHALL BE 0.1 MAX.
 2 WHEN THIS CONNECTOR MATES WITH DF14-S-1.25C, THE MATTING LENGTH IS 7.3mm.
 3 FOR CONNECTORS, 2 OR 3 CONTACTS, SIMPLIFIED LOCK HOLE SHALL BE SET AT THE CENTER OF HOUSING.



2	BRASS	CONTACT AREA: GOLD PLATED $0.1\mu\text{m min}$ LEAD AREA: TIN-COPPER PLATED $1\mu\text{m min}$	5	POLYESTER	CLEAR (COVER TAPE)
			4	A-PET	CLEAR (EMBOSSED CARRIER TAPE)
1	POLYAMIDE	UNDER PLATING: NICKEL PLATED $1\mu\text{m min}$ BEIGE, UL 94V-0	3	PHOSPHOR BRONZE	TIN-COPPER PLATED $1\mu\text{m min}$ UNDER PLATING: NICKEL PLATED $0.5\mu\text{m min}$
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD) CL					DRAWN F. Mustafa 03. 3. 5	DESIGNED I. Donkanya 03. 3. 17	CHECKED T. Mung'uchi 03. 03. 25	APPROVED T. Mung'uchi 03. 03. 25	RELEASED
DRAWING NO. EDC3-160309-19		PART NO. DF14A-*P-1.25H(56)							
SCALE 5 : 1		CODE NO.		CL538-					
UNITS mm		HIROSE ELECTRIC CO., LTD		1/2					

TO				
----	--	--	--	--



NOTE 4 1 REEL : 1000 CONNECTORS
5 AT THE BEGINNING OF THE REEL , 30 COMPONENTS SHALL BE EMPTY .
6 AT THE END OF THE REEL , 20 COMPONENTS SHALL BE EMPTY .
WHEN THE TAPE WIDTH IS 44 TO 56mm , SPROCKET HOLES SHALL BE SET ON BOTH SIDES OF REEL AS SHOWN ON THIS DRAWING .

TO

HR5

HIROSE ELECTRIC CO., LTD

CL538-

2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[DF14A-4P-1.25H\(56\)](#)