










MATED HIGHT (h)		(mm)
RECEPTACLE NO.	HEADER NO.	
DF17A(3.0)-40DS-0.5V(57)		
DF17#(2.0)-40DP-0.5V(57)		5
DF17#(4.0)-40DP-0.5V(57)		7



- NOTES
- 1: LEAD CO-PLANARITY INCLUDE REINFORCED METAL FITTINGS SHALL BE 0.1mm MAX.
 - 2: WHEN A PART MARKED WITH  HAS A PATTERN BUT NO RESIST ON IT. TAKE CARE TO PREVENT THE CONNECTOR FROM TOUCHING IT.

2	POLYAMIDE (PA6T)	WHITE BEIGE . UL94V-0			
1	PHOSPHOR BRONZE	CONTACT AREA:GOLD PLATED 0.1µm min LEAD AREA:GOLD PLATED 0.02µm min UNDER PLATING : NICKEL 1µm min	5	PS	BLACK (PLASTIC REEL)
			4	POLYESTER	CLEAR (COVER TAPE)
			3	A-PET	CLEAR (EMBOSSED CARRIER TAPE)
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 5 : 1	COUNT △		DESCRIPTION OF REVISIONS
 HIROSE ELECTRIC CO., LTD.		APPROVED : KH. IKEDA	08.11.20	DRAWING NO. EDC3-161648-02	
		CHECKED : TS. MIYAZAKI	08.11.20	PART NO. DF17A(3.0)-40DS-0.5V(57)	
		DESIGNED : TY. YAMASAKI	08.11.19	CODE NO. CL683-0014-1-57	
		DRAWN : TY. YAMASAKI	08.11.19	△ 1/2	
		DESIGNED		CHECKED	DATE

Sep.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[DF17A\(3.0\)-40DS-0.5V\(57\)](#)