






Sep.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




MATED HIGHT (h)		(mm)	
HEADER NO.	RECEPTACLE NO.	DF17*(3.0)-40DS-0.5V(57)	DF17*(4.0)-40DS-0.5V(57)
DF17A(4.0)-40DP-0.5V(57)		7	8




RECOMMENDED PATTERN





A-A(10:1)



- NOTES 1 LEAD CO-PLANARITY INCLUDE REINFORCED METAL FITTINGS SHALL BE 0.1 mm MAX.
- 2 WHEN A PART MARKED WITH  HAS A PATTERN BUT NO RESIST ON IT. TAKE CARE TO PREVENT THE CONNECTOR FROM TOUCHING IT.

1	PHOSPHOR BRONZE	CONTACT AREA:GOLD PLATED 0.1μm min	5	PS	PLASTIC REEL . BLACK			
		LEAD AREA:TIN PLATED 1μm min	4	POLYESTER	CLEAR (COVER TAPE)			
		UNDER PLATING:NICKEL PLATED 1μm min	3	A-PET	CLEAR (EMBOSSED CARRIER TAPE)			
			2	POLYAMIDE (PA6T)	NATURAL (BEIGE).UL94V-0			
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS			
UNITS mm		SCALE 5 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.	APPROVED :KH. IKEDA		08.09.25		DRAWING NO. EDC3-161768-02			
	CHECED :TS. MIYAZAKI		08.09.25		PART NO. DF17A(4.0)-40DP-0.5V(57)			
	DESIGNED :TY. YAMASAKI		08.09.03		CODE NO. CL683-0134-3-57			
	DRAWN :TY. YAMASAKI		08.09.03		 1/2			

Sep.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



DETAIL OF PART NO. LABEL

SUPPLIER	生産月日	年 月 日
QUANTITY	図 番	CL683-0134-3-57
PART NO.	品 名	DF17A(4.0)-40DP-0.5V(57)
CODE NO.	納入数量	1000 KO
DATE OF MANUFACTURED	納入者	ヒロセ電機(株)

HRS	DRAWING NO.	EDC3-161768-02	
	PART NO.	DF17A(4.0)-40DP-0.5V(57)	
	CODE NO.	CL683-0134-3-57	$\triangle$ 2/2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[DF17A\(4.0\)-40DP-0.5V\(57\)](#)