








A
B
C
D
E
F




RECOMMENDED PCB LAYOUT(5:1)
(PCB THICKNESS:1.6±0.1)



HRS DRAWING FOR REFERENCE




APPLICATION DIAGRAM(3:1)



PART No.	CODE No.	NUMBER OF CONTACT	A	B
DF1EC- 2P-2.5DSA(36)	CL541-0867-4-36	2	2.5	7.5
DF1EC- 3P-2.5DSA(36)	CL541-0868-7-36	3	5.0	10.0
DF1EC- 4P-2.5DSA(36)	CL541-0869-0-36	4	7.5	12.5
DF1EC- 5P-2.5DSA(36)	CL541-0870-9-36	5	10.0	15.0
DF1EC- 6P-2.5DSA(36)	CL541-0871-1-36	6	12.5	17.5
DF1EC- 7P-2.5DSA(36)	CL541-0872-4-36	7	15.0	20.0
DF1EC- 8P-2.5DSA(36)	CL541-0873-7-36	8	17.5	22.5
DF1EC- 9P-2.5DSA(36)	CL541-0874-0-36	9	20.0	25.0
DF1EC-10P-2.5DSA(36)	CL541-0875-2-36	10	22.5	27.5
DF1EC-11P-2.5DSA(36)	CL541-0876-5-36	11	25.0	30.0
DF1EC-12P-2.5DSA(36)	CL541-0877-8-36	12	27.5	32.5
DF1EC-13P-2.5DSA(36)	CL541-0878-0-36	13	30.0	35.0
DF1EC-14P-2.5DSA(36)	CL541-0879-3-36	14	32.5	37.5
DF1EC-15P-2.5DSA(36)	CL541-0880-2-36	15	35.0	40.0

- NOTES 1 CONFIGURATION OF DF1EC-2P-2.5DSA(36), DF1EC-3P-2.5DSA(36) AND DF1EC-4P-2.5DSA(36).
2 AND 3 OF CONTACTS MAKE DRAWING FORM (PROJECTION) UNNECESSARY, AND
4 OF CONTACTS CONSIDERED AS ONE PROJECTION IN THE CENTER.
3. UL(FILE NO.E52653).
C-UL(FILE NO.E52653) APPROVED PRODUCT.



1			POLYAMIDE		NATURAL (BEIGE)・UL94V-0		2		BRASS		SURFACE:GOLD PLATED 0.2μm min								
											UNDER PLATING:NICKEL PLATED 1μm min								
NO.		MATERIAL		FINISH . REMARKS				NO.		MATERIAL		FINISH . REMARKS							
UNITS mm				SCALE 2 : 1				COUNT		DESCRIPTION OF REVISIONS				DESIGNED		CHECKED		DATE	
 HIROSE ELECTRIC CO., LTD.						APPROVED :KI. AKIYAMA				15. 05. 23		DRAWING NO.		EDC-161943-36-00					
						CHECKED :TS. FUKUSHIMA				15. 05. 23		PART NO.		DF1EC- *P-2. 5DSA(36)					
						DESIGNED :TS. KUMAZAWA				15. 05. 23		CODE NO.		CL541-					
						DRAWN :MI. SAKIMURA				15. 05. 23				 1/1					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[DF1EC-11P-2.5DSA\(36\)](#)