








	△數 COUNT	訂正事項 DISCRIPTION OF REVISIONS	擔當 B Y	檢圖 CHKD	年 月 日 DATE		△數 COUNT	訂正事項 DISCRIPTION OF REVISIONS	擔當 B Y	檢圖 CHKD	年 月 日 DATE
△					. .	△					. .
△					. .	△					. .
△					. .	△					. .




NOTE



1. SOLDERING TEMPERATURE : 250°C PEAK, 10sec MAX.
2. OPERATING TEMPERATURE : -55°~105°C
3. USED REFLOW SYSTEM : IN THE AIR OR NITROGEN
4. NO. OF CYCLES : 2 MAX
5. MATING PART
FEMALE : DF51K-4S-2C
6. CO-PLANARITY : 0.12 MAX.
7. RECOMMENDED PCB THICKNESS IS 1.6mm.
8. RECOMMENDED SOLDER THICKNESS IS 0.15mm
9. UL(File No. E132750) AUTHORIZATION ARTICLE.
C-UL(File No. E132750) AUTHORIZATION ARTICLE.



CAP COMBINATION (2:1)



4	LCP	BLACK			
3	BRASS	TIN PLATED : 1μm MIN UNDER PLATING : NICKEL 1μm MIN			
2	BRASS	TIN PLATED : 1μm MIN UNDER PLATING : NICKEL 1μm MIN	8	PS	REEL BOBBIN
			7	PET	COVER TAPE
			6	CONNECTOR	DF51K-4P-2V
1	LCP	BLACK	5	PS	EMBOSS CARRIER TAPE
NO.	MATERIAL	FINISH,REMARKS	NO.	MATERIAL	FINISH,REMARKS

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
					

	DRAWING NO. EDC3-633593		PART NO. DF51K-4P-2V (800)	
	SCALE 5:1 UNITS mm		CODE NO CL 6652-0091-4-800	
 HIROSE KOREA CO.,LTD.			1 2	

F

8

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[DF51K-4P-2V\(800\)](#)