

1 2 3 4

A A

B B

C C

D D

E E

F F

1 2 3 4

NOTE 1 We indicate the length of the harness on the last of product name, 'L' part.

2 Tolerance for [L]

Length L [mm]	Tolerance [mm]
35 \leq L \leq 200	± 4
200 $<$ L \leq 500	± 8
500 $<$ L \leq 1000	± 12
1000 $<$ L	$\pm 1.5\%$

3 Connector rotation angle is within ± 45 degree from the above image.
 For long length in the case of L>500, the angle is optional.

4. Specifications are subject to change without notice.

[DIMENSIONS OF CONNECTOR]

For stable supply of this series,
 material supplier of piece part#1
 will be changed during 2019-2022.
 Please note this change in advance.
 There will be no difference in product
 performance and quality.

1	W.FL-LP-040HF(06)	CL331-0563-6-06	2	0.81 Dia. coaxial cable	HALOGEN FREE		
NO.	PART NO.	CODE NO.	NO.	PART NO.			
UNITS mm		SCALE FREE	COUNT 2	DESCRIPTION OF REVISIONS DIS-D-00003630	DESIGNED MS. MATSUMOTO	CHECKED MT. KANEKO	DATE 20181031

HRS HIROSE ELECTRIC CO., LTD.	APPROVED : NK. NINOMIYA	20180607	DRAWING NO. PART NO. WFL-2LPHF6-04**TV-A-L CODE NO.
	CHECKED : MT. KANEKO	20180606	
	DESIGNED : MS. MATSUMOTO	20180606	
	DRAWN : MS. MATSUMOTO	20180606	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[WFL-2LPHF6-04N1TV-A-500](#)