


[illegible]

NOTE 1 REFERENCE IS A.

2 LEAD CO-PLANARITY SHALL BE 0.1 MAX.

3 THICKNESS OF SUPPORTING TAPE SHALL BE 0.188(7.5mil) MIN.

4 THIS PRODUCT SATISFIES HALOGEN FREE REQUIREMENTS DEFINED AS 900 PPM MAXIMUM CHLORINE, 900 PPM MAXIMUM BROMINE, AND 1500 PPM MAXIMUM TOTAL OF CHLORINE AND BROMINE.

5	BRASS	TIN PLATING 1μMIN OVER NICKEL 1μMIN					
4	BRASS	TIN PLATING 1μMIN OVER NICKEL 1μMIN	9	(CONNECTOR)			
3	PHOSPHOR BRONZE	GOLD PLATING 0.05μMIN OVER NICKEL 1μMIN	8	POLYSTYRENE			
2	LCP	(BLACK) UL94V-0	7	POLYESTER			
1	LCP	(GRAY) UL94V-0	6	POLYSTYRENE			
NO.	MATERIAL	FINISH .	REMARKS	NO.	MATERIAL	FINISH .	REMARKS

UNITS mm		SCALE 5 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.	APPROVED : NM. NISHIMATSU		11. 04. 26		DRAWING NO. EDC3-159052-02			
	CHECED : HS. SAKAMOTO		11. 04. 26		PART NO. FH28D-30(15)SB-1SH(05)			
	DESIGNED : RT. IKEDA		11. 04. 26		CODE NO. CL586-1860-1-05			
	DRAWN : NM. SANPEI		11. 04. 26		 1/2			

Sep.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

EMBOSSED CARRIER TAPE DIMENSION (2 : 1)

REEL DIMENSION(FREE)

DIRECTION OF UNREELING

NOTE 5 THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

6 PER REEL : 2000 CONNECTORS.

7 REFER TO JIS C 0806 (PACKAGING OF COMPONENTS FOR AUTOMATIC HANDLING).

DRAWING FOR PACKING

HRS

DRAWING NO.	EDC3-159052-02		
PART NO.	FH28D-30<15>SB-1SH<05>		
CODE NO.	CL586-1860-1-05		$\triangle$ 2/2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[FH28D-30\(15\)SB-1SH\(05\)](#)