

DRAWING FOR REFERENCE: This is subject to change without notice
08/11/2012

TO
RF

1					2					3					4				
COUNT	DESCRIPTION OF REVISIONS				BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS				BY	CHKD	DATE				
△								△											
△								△											
△								△											
△								△											

Top View Dimensions:
Overall width: 12.7±0.3
Inner width: 8.64±0.1
Overall height: 12.7±0.3
Inner height: 8.64±0.1
Holes: 4-φ2.6±0.1

Side View Dimensions:
Total height: 18.75±0.3
Section 1 height: 9.55±0.2
Section 2 height: 1.7±0.2
Section 3 height: 8±0.2
Bottom hole diameter: φ5.3±0.2

Callouts:
1: HRM(SMA)
2: 1/4-36UNS-2A
3: PRESS FITTING
4: PRICK PUNCH (2 POINT)
5: PRESS FITTING
U.FL

3	PTFE			5	BRASS		NICKEL PLATING		
2	BERYLLIUM COPPER		GOLD PLATING	4	PTFE				
1	BRASS		NICKEL PLATING						
NO.	MATERIAL		FINISH, REMARKS		NO.	MATERIAL		FINISH, REMARKS	

CODE NO. (OLD)		DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
RoHS COMPLIANT		R.KIMURA	R.KIMURA	M. Yamane	J. Mutani	
		05.08.11	05.08.11	05.08.23	05.08.26	

 SCALE 5 : 1 UNITS mm	DRAWING NO. EDC4-300041-40		PART NO. HRMJ-U.FLJ-PA-1(40)	
	HRS HIROSE ELECTRIC CO.,LTD.		CODE NO. CL311-0364-5-40	
			1 1	

FORM NO.228



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[HRMJ-U.FLJ-PA-1\(40\)](#)