

COUNT		DESCRIPTION OF REVISIONS		BY	CHKD	DATE	COUNT		DESCRIPTION OF REVISIONS		BY	CHKD	DATE

Note 1 Applicable Crimp Contact:HR12-SC-212,112
(Applicable Wire:AWG#26~#30,
Jacket Dia.φ1 Max)

2 Applicable Crimp Contact Extraction Tool
:HR12-SC-TP

Top View Dimensions:
Overall width: 21±0.5
Inner width: 16±0.15
Bottom width: 14.5±0.15
Overall height: 20±0.5
Hole diameter: φ2.2±0.2

Side View Dimensions:
Overall height: 15.5±1
Base height: 10±0.5
Hole diameter: (φ14.1)

Callouts: 1, 2, 3, 4

HRS DRAWING FOR REFERENCE

2	Phosphor bronze	Tin plated	4	Brass	JIS B 1181 Hexagon Nut M2x0.4, No. 3
1	PBT	(Black)	3	Brass	Tin plated
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
CODE NO. (OLD)		DRAWN	DESIGNED	CHECKED	APPROVED
		H. Kishi	H. Kishi		M. Yoshida
		95.5.15	95.5.15		95.5.19
DRAWING NO. EDC3-028887		PART NO. HR12-14RA-20SC			
SCALE 1 : 1		CODE NO. CL112-1504-8		1	
UNITS mm		HIROSE ELECTRIC CO., LTD.		FORM NO. 229	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[HR12-14RA-20SC](#)