


| PART No.                | CODE No. | PIN | A    | B   | C   |
|-------------------------|----------|-----|------|-----|-----|
| KN13CO.7-10DP-0.4V(895) | -        | 10  | 3.48 | 1.6 | 1.6 |
| KN13CO.7-16DP-0.4V(895) | -        | 16  | 4.68 | 2.8 | 2.8 |
| KN13CO.7-24DP-0.4V(895) | -        | 24  | 6.28 | 4.4 | 4.4 |
| KN13CO.7-30DP-0.4V(895) | -        | 30  | 7.48 | 5.6 | 5.6 |

2. CONTACT PLATING SPECIFICATIONS.  
CONTACT AREA : GOLD 0.05  $\mu$ m MIN.  
SMT LEAD : GOLD 0.05  $\mu$ m MIN.  
UNDER PLATING : NICKEL 1  $\mu$ m MIN.  
( SURFACE : SEALING )

3. EACH CONTACTS 4 CORNERS ARE PROVIDED FOR MOUNTING (NOT FOR ELECTRICAL CONNECTION)

4. PLEASE CONTACT US IN CASE YOU WILL MAKE DIFFERENT SETTINGS FROM OUR RECOMMENDATION.

[illegible]

| P I N | D   | E  | F    | G    | H    |
|-------|-----|----|------|------|------|
| 10    | 5.5 | 12 | 3.59 | 13.5 | 17.5 |
| 16    | 7.5 | 16 | 4.79 | 17.5 | 21.5 |
| 24    | 7.5 | 16 | 6.39 | 17.5 | 21.5 |
| 30    | 7.5 | 16 | 7.59 | 17.5 | 21.5 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[KN13C0.7-30DP-0.4V\(895\)](#)