




	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
1	1	RE-E-06282	N.N	S.M	99.5.24					
2	2	RE-E-06362	N.N	S.M	99.6.21					
3	4	RE-E-06453	N.N	S.H	99.8.24					

TABLE-1

CONTACT CODE	APPLICABLE WIRE	RATED VOLTAGE
PX50-SC-※31 (※印→1 LOOSE PIECE)	AWG # 16	10A
(※印→2 STRIP)	AWG # 18	8A



(revised configuration) Δ^1

(revised configuration) Δ_3

NOTES 1 APPLICABLE CONTACT, APPLICABLE WIRE AND RATED VOLTAGE IS SHOWN IN TABLE 1.
SPECIFIED CURRENTS ARE RATED VALUE PER CONTACT.
(60A PER 6 CONTACTS FOR AWG#16 WIRE)

2 .NOT FOR INTERRUPTING CURRENT .

3 .ORDER TO BE MADE PER 100PCS.

		DRAWING NO.		PART NO.			
		EDC3-121227		PX50-AF6S			
SCALE							
2 : 1							
UNITS		mm		HIROSE ELECTRIC CO., LTD.		CODE NO.	
						CL236-0002-2	
						1/1	

TO	Q1			
----	----	--	--	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[PX50-AF6S](#)