



- NOTES
- 1 THE RECOMMENDED CLAMP TORQUE, REF.NO.①: 0.15 TO 0.2N·m.  
LOCTITE 263, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF.NO.① FROM LOOSENING.
  - 2 APPLICABLE CABLE:  $\phi 14 \pm 0.3$
  - 3 ASSEMBLE WITH APPLICABLE CONNECTOR (RM24WTP-\*\*(85)).  
\*\* SHOWS NUMBER OF CONTACT, AND MALE OR FEMALE OF CONNECTOR.
  - 4 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE PLEASE CONFIRM BEFORE THE USE.

3	BRASS	NICKEL PLATING			
2	PHOSPHOR BRONZE	NICKEL PLATING	5	BRASS	NICKEL PLATING
1	BRASS	NICKEL PLATING	4	CHLOROPRENE RUBBER	(BLACK)
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 2	DESCRIPTION OF REVISIONS DIS-C-00002214	DESIGNED HY. KISHI
					CHECKED HY. KOBAYASHI
					DATE 18. 04. 17
HIROSE ELECTRIC CO., LTD.		APPROVED : HY. KOBAYASHI	18. 02. 22	DRAWING NO.	EDC-110117-31-00
		CHECKED : HY. KOBAYASHI	18. 02. 22	PART NO.	RM24WTP-CP(14)(31)
		DESIGNED : HY. KISHI	18. 02. 21	CODE NO.	CL109-1495-6-31
		DRAWN : MK. INOUE	18. 02. 07		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[RM24WTP-CP\(14\)\(31\)](#)