


Jan.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES
- 1 THE RECOMMENDED CLAMP TORQUE, REF.NO. ⑧ : 3 TO 4 N · m.  
LOCTITE 243, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF.NO. ⑧ FOR LOOSENING.
  - 2 ACROSS FLATS HEXAGON HEAD OF REF.NO. ⑬ : 1.27  
THE RECOMMENDED CLAMP TORQUE, REF.NO. ⑬ : 0.2 TO 0.3 N · m.  
LOCTITE 243, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF.NO. ⑬ FOR LOOSENING.
  - 3 THIS PRODUCTS TO BE USED WITH CABLE CLAMP, JR13WCC-※(32).  
※ DESIGNATE DIAMETER(mm) OF APPLICABLE CABLE.  
THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER.  
DEPENDING ON THE CABLE STRUCTURE.  
PLEASE CONFIRM BEFORE THE USE.
  - 4 ONE EXAMPLE OF THE ROTATION OF REF.NO. ⑧, ⑨ TO REF.NO. ① IS SHOWN.
  - 5 SURFACE AREA:GOLD PLATING 0.2  $\mu$ m min.  
UNDER PLATING:NICKEL PLATING 3  $\mu$ m min.

6	BRASS	NICKEL PLATING	12	STAINLESS STEEL	JISB1177 HEX SOKET SET SCREW M2.6×0.45×2
5	ACRYLONITRILE BUTADIENE RUBBER	(GRAY)	11	POLYACETAL	(WHITE)
4	DIALLYL PHTHALATE	(BLACK) UL94V-0	10	ACRYLONITRILE BUTADIENE RUBBER	(GRAY)
3	DIALLYL PHTHALATE	(BLACK) UL94V-0	9	BRASS	NICKEL PLATING
2	COPPER ALLOY	5	8	BRASS	NICKEL PLATING
1	BRASS	NICKEL PLATING	7	PHOSPHOR BRONZE	NICKEL PLATING
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-C-00003899	DESIGNED TY. SUZUKI	CHECKED HY. KOBAYASHI	DATE 20200324
HIROSE ELECTRIC CO. , LTD.		APPROVED	: HY. KOBAYASHI	20180222	DRAWING NO. EDC-114786-32-00		
		CHECKED	: HY. KOBAYASHI	20180222	PART NO. RM15WTLP-8S(32)		
		DESIGNED	: HY. KISHI	20180221	CODE NO. CL109-1889-1-32		
		DRAWN	: MK. INOUE	20180213			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[RM15WTLP-8S\(32\)](#)