





- Notes
- 1 Applicable crimping contact : RP19-SC-222(CL113-0266-2)
(Applicable wire : AWG #24 to #28)
 - 2 Applicable crimp contact crimping tool : RP13A-TC-01(CL150-0070-0)
Applicable crimp contact extraction tool : RP6-SC-TP(CL150-0039-0)
 - 3 The recommended tightening torque of Ref.No. ⑥ shell be 0.2N · m.
 - 4 This product is delivered disassemble.
 - 5 The cable pull and twisting strength and other characteristics may differ.
Depending on the cable structure, please confirm before the use.

4	Brass								
3	Polycarbonate	(Black)	UL94V-0	7	Flexible polyvinylchloride	(Black)			
2	Polycarbonate	(Black)	UL94V-0	6	Brass	Black chromate treatment(Trivalent chromium) JIS B1111 M2×0.4×4			
1	Polycarbonate	(Black)	UL94V-0	5	Steel	Nickel plating			
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS			
UNITS mm		SCALE 2 : 1		COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.		APPROVED		·EJ. KUNII	16. 03. 23	DRAWING NO. EDC-028674-71-00			
		CHECKED		·EJ. KUNII	16. 03. 23	PART NO. RP13A-12PK-20SC(71)			
		DESIGNED		·MM. ISHII	16. 03. 23	CODE NO. CL113-1012-0-71			
		DRAWN		·MM. ISHII	16. 03. 23	 1/1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[RP13A-12PK-20SC\(71\)](#)