



Sep.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

CONNECTOR AFTER COMPONENTS INSTALLED



3 PATTERN OF MOUNTING METAL CLAMP AND CABLE BUSHING



1. MISINSERTION PREVENTION KEY TYPE: 2B
2. PACKAGING: COMPONENTS ARE PACKED SEPARATELY BY THE TYPES OF PARTS WITH CROSS-CARRIED TAPPING SCREWS(REF No.10) ATTACHED.
3. METAL CLAMP AND CABLE BUSHING ARE SEPARATELY AVAILABLE.

| | | |
|---------------|---------------|--------------|
| METAL CLAMP | ST40X-CM(5.8) | CL241-0024-0 |
| CABLE BUSHING | ST40X-BS(5.8) | CL241-0025-3 |

4. COVER CASE (A) AND (B) SHALL BE FITTED ONLY ONE TIME DUE TO THEIR PRESS FITTING DESIGN.
5. PLEASE REFER TO THE ASSEMBLY MANUAL 'ETAD-E2720'.

| | | | | | |
|---------------------------|-----------------|---|-----------|--------------------------|-----------------------------|
| 4 | STAINLESS STEEL | | 10 | STEEL | BLACK |
| 3 | COPPER ALLOY | CONTACT PORTION:GOLD PLATED 0.2 μ m MIN POST PORTION :GOLD PLATED 0.03 μ m MIN | 9 | POLYCARBONATE | UL94V-0 BLACK |
| 2 | COPPER ALLOY | CONTACT PORTION:GOLD PLATED 0.2 μ m MIN POST PORTION :GOLD PLATED 0.03 μ m MIN | 8 | POLYCARBONATE | UL94V-0 BLACK |
| 1 | POLYAMIDE | UL94V-0 BLACK | 7 | STAINLESS STEEL | |
| | | | 6 | STAINLESS STEEL | |
| | | | 5 | STAINLESS STEEL | |
| NO. | MATERIAL | FINISH , REMARKS | NO. | MATERIAL | FINISH , REMARKS |
| UNITS mm | | SCALE 2 : 1 | COUNT | DESCRIPTION OF REVISIONS | DESIGNED CHECKED DATE |
| HIROSE ELECTRIC CO., LTD. | | APPROVED : NM. NISHIMATSU | 16.03.01 | DRAWING NO. | EDC-126195-30-00 |
| | | CHECKED : NM. NISHIMATSU | 16.03.01 | PART NO. | ST40X-18S-CV1(30) |
| | | DESIGNED : TS. ITO | 16.03.01 | CODE NO. | CL241-0062-0-30 |
| | | DRAWN : AK. AKIYAMA | 16.03.01 | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[ST40X-18S-CV1\(30\)](#)