





		DESCRIPTION OF REVISIONS		BY	CHKD	DATE			DESCRIPTION OF REVISIONS		BY	CHKD	DATE
	COUNT							COUNT					
△						•	•	△					•
△						•	•	△					•
△						•	•	△					•



APPLICABLE CABLE		
	INSULATION (φmm)	0.90~ 1.00
	JACKET (φmm)	(φ3.6) *1
	DRAIN WIRE	(7/φ0.18) AWG25

NOTES: 1.() INDICATES THE REFERENCE DIMENSIONS.
 2>APPLICABLE CABLE DIMENSIONS AS SHOWN IN TABLE-1.
 *(1)THIS IS FOR REFERENCE.
 (DIMENSION VARIES ACCORDING TO JACKET HARDNE

1		POLYCARBONATE		TRANSPARENCY		2		PHOSPHOR BRONZE		GOLD PLATING 1.27 μ m					
NO.		MATERIAL		FINISH, REMARKS		NO.		MATERIAL		FINISH, REMARKS					
CODE NO. (OLD)						DRAWN		DESIGNED		CHECKED		APPROVED		RELEASED	
						S. Sato		S. Sato		T. Watanabe		Matsuzaki			
						01-09-03		01-09-03		01-09-03		01-09-03		.	
DRAWING NO.				PART NO.				TM4P-64P							
EDC3-010354															
SCALE															
5 : 1															
UNITS															
mm				HRS				HIROSE ELECTRIC CO., LTD				CL222-0280-2			
								CODE NO.				1			

TO	Q2			
----	----	--	--	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[TM4P-64P](#)