

1		2		3		4	
A		B		C		D	
E		F					

Part No.	Cable color
~068*1~	GRAY
~068*2~	BLACK
~068*3~	WHITE

NOTE ① We indicate the length of the harness on the last of product name, 'L' part.

② Tolerance for [L]

Length L [mm]	Tolerance [mm]
100 ≤ L ≤ 200	±4
200 < L ≤ 500	±8
500 < L ≤ 1000	±12
1000 < L	±1.5%

③ Connector rotation angle is within ±45 degree from the above image.
For long length in the case of L>500, the angle is optional.

4. Specifications are subject to change without notice.

【 DIMENSIONS OF CONNECTOR 】

1	X.FL-LP(P)-068	CL331-0714-0	2	1.13 Dia. coaxial cable	HALOGEN FREE
NO.	PART NO.	CODE NO.	NO.	PART NO.	

UNITS mm		SCALE FREE	COUNT ① 2	DESCRIPTION OF REVISIONS DIS-D-00003339	DESIGNED MS. MATSUMOTO	CHECKED MT. KANEKO	DATE 18. 07. 12
-------------	--	---------------	--------------	--	---------------------------	-----------------------	--------------------

	APPROVED	・NK. NINOMIYA	16. 07. 23	DRAWING NO.	X. FL-2LPP-068**TS-A-L	①
	CHECKED	・MT. KANEKO	16. 07. 23	PART NO.		
	DESIGNED	・MS. MATSUMOTO	16. 07. 23	CODE NO.		
	DRAWN	・MS. MATSUMOTO	16. 07. 23			

FORM HC0011-5-1
2
3
4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[X.FL-2LPP-068K3TS-A-\(500\)](#)