

HOME > Product Info

Product Category

Product Info

1 Products

	1-1	
Product No.	UM-R-PC(41)	
HRS No.	318-0032-0 41	
Status	In Production	
RoHS	Yes	
Series	UM	
Category	Coaxial Connectors	
No. of Positions	N/A	
Contact Mating Area Plating	Gold	
Contact Gender	Male	
Connector Type	Board mounting	
PCB Mount Type	Throughhole	
Current Rating(Amps)(Max.)	N/A	
Impedance (ohm)	50	
Frequency (GHz)(Min)	0	
Frequency (GHz)(Max)	1	
V.S.W.R. (Max)	1.2	
Termination Style	N/A	
Temperature (deg C)	-55 to 85	
Mating/Unmating Cycles	1000	
Applicable Cable	N/A	
Generic Name	N/A	
Selling Unit	1pcs.(1pcs.)	
General Description	Pushon type(Q); Receptacle	
Inquiry	REQUEST	
Similar Products	Similar Products ▶ 3 products	
e-Commerce	E-Commerce ▶	
Product No.	UM-R-PC(41)	
HRS No.	318-0032-0 41	

1-1

[▶ Terms of Service](#)
[▶ RoHS](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[UM-R-PC\(41\)](#)