



1 Products

1-1

Product No.	POB-LP-58/U(40)
HRS No.	326-0027-4 40
Status	In Production
RoHS	Yes
Series	POB
Category	Coaxial Connectors
No. of Positions	N/A
Contact Mating Area Plating	Gold
Contact Gender	Male
Connector Type	Cable
PCB Mount Type	N/A
Current Rating(Amps)(Max.)	N/A
Impedance (ohm)	50
Frequency (GHz)(Min)	0
Frequency (GHz)(Max)	12.4
V.S.W.R. (Max)	1.3
Termination Style	Soldering
Temperature (deg C)	-55 to 85
Mating/Unmating Cycles	500
Applicable Cable	RG58/U
Generic Name	N/A
Selling Unit	1pcs.(1pcs.)
General Description	Plug; Right angle; Pushpull lock
Inquiry	REQUEST
Similar Products	N/A
e-Commerce	E-Commerce 
Product No.	POB-LP-58/U(40)
HRS No.	326-0027-4 40

1-1

 Terms of Service  RoHS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[POB-LP-58/U\(40\)](#)