

MICRO SWITCHFREEPORT ILLINOIS, U. S. A
A DIVISION OF HONEYWELL INC.
FED. MFG. CODE 91929**SWITCH - BASIC**

CATALOG LISTING

10BS228**10BS228****M**DRAWING
NUMBER**X**

ISSUE

3

REPLACES X84699 - 10BS

RELEASE NO. PR-15873

CHECK

REVISIONS

A	CO-1	73267-C
	J A	
	20 OCT 93	
B	CO-1	80988
	J J A	
	5 JUN 95	

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

3X 8-32 UNC (.219) BINDING
HEAD COMBINATION TERMINAL
SCREW AND CUPWASHER

COMMON TERMINAL


NORMALLY OPEN TERMINAL

NORMALLY CLOSED
TERMINAL**NOTES**

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF
.139 MAX DIA ON 1.000±.002 CENTERS
- 2 - ADJUSTING SCREW BUSHING IS AT SAME ELECTRICAL
POTENTIAL AS NORMALLY CLOSED TERMINAL

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF
HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

**CHARACTERISTICS**

OPERATING FORCE - - - - 32 OZ MAX

RELEASE FORCE - - - - - 10 OZ MIN

DIFFERENTIAL TRAVEL - - - - .010 MIN

OVERTRAVEL - - - - - .010 MIN

ELECTRICAL DATACONTACT ARRANGEMENT
S P D T20A 125, 250 OR 480 VAC
3/4 HP 125 VAC, 1 1/2 HP 250 VAC

60 / 75° (CU)

SCALE FULL

DO NOT
SCALE PRINTUNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) ± .030

TWO PLACE (.00) ± .015

THREE PLACE (.000) ± .005

ANGLES ± 10°

RAW MATERIAL - COMMERCIAL STANDARD

DIMENSIONS ARE IN INCHES AND ARE
TO BE MET BEFORE PROTECTIVE
COATINGS ARE APPLIED

MICRO SWITCH STANDARDS APPLY

WEIGHT

FO-52848-B

DRAWN

MAM

1 SEP 87

CHECK

3 SEP 87

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[10BS228](#)