




MICRO SWITCH
FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH - ENCLOSED

CATALOG LISTING
201EN1-1



NOTES:

- 1 - CORROSION RESISTANT STEEL ENCLOSURE
- 2 - SWITCH SEALED PER MIL-S-8805 SYMBOL 4
- 3 - CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
- 4 - COINCIDENCE OF OPERATING AND RELEASING POINTS:
.010 OF PLUNGER TRAVEL
- 5 - REPLACEMENT MOUNTING HARDWARE PACKET 19PA71 WHICH CONTAINS STAINLESS STEEL HARDWARE
- 6 - ELECTRICAL RATINGS APPLY AS SPECIFIED IN MIL-S-8805/40-1 UP TO 185°F
- 7 - HARDWARE FURNISHED ASSEMBLED
- 8 - SWITCH PLUNGER SEAL VITON ELASTOMER

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA		
OPERATING FORCE ----- 6-12 LB	CONTACT ARRANGEMENT		
FULL OVERTRAVEL FORCE ----- 30 LB MAX	S P D T (2)		
RELEASE FORCE ----- 4 LB MIN	LOAD	28 VDC 	
PRETRAVEL ----- .040 MAX		SEA LEVEL	50,000 FT.
DIFFERENTIAL TRAVEL ----- .020 MAX		RES	4
OVERTRAVEL ----- .250 MIN		IND	2
		MOTOR	4

SCALE FULL			
DO NOT SCALE PRINT			
TOLERANCES			
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±			
DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/16	X
ONE PLACE	X,X	0.4/018	X,X
TWO PLACES	X,XX	0.15/006	X,XX
THREE PLACES	X,XXX	0.06/003	X,XXX
ANGLES			
DESIGN UNITS		US CUSTOMARY	
THIRD ANGLE PROJECTION			
WEIGHT 7.5 OZ MAX			

201EN1-1

M

DRAWING NUMBER

26

ISSUE

26

REVISIONS

A	REL	PR-12383
	J A P	29 AUG 83
B	CO57370	
	T SK	15 MAY 85
E	CO58255	
T	A D	5 DEC 85
D	CO74101	
	DAW	10 FEB 93
E	CO-77504-C	
	DLT	27 JUL 94

FO-52851-B

DRAWN

J A P 29 AUG 83

CHECK

DJC

24 AUG 83

RELEASE NO. PR-12383

REPLACES

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[201EN1-1](#)