



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH				THIRD ANGLE PROJECTION 	
CHARACTERISTICS		ELECTRICAL DATA		SCALE	FULL
OPERATING FORCE	6-12 LB	CONTACT ARRANGEMENT		DO NOT SCALE PRINT	
FULL OVERTRAVEL FORCE	30 LB MAX	S P D T (2)		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE	4 LB MIN	LOAD	28 VDC		ONE PLACE (.0) ±.030
PRETRAVEL	.040 MAX		SEA LEVEL	50,000 FT.	TWO PLACE (.00) ±.015
DIFFERENTIAL TRAVEL	.020 MAX	RES	4	4	THREE PLACE (.000) ±.005
OVERTRAVEL	.250 MIN	IND	2	2	ANGLES ±
		MOTOR	4		WEIGHT 7.0 OZ APPROX
		LAMP			

- NOTES**
- ① CORROSION RESISTANT STEEL ENCLOSURE (ENCLOSURE IS NOT PAINTED)
 - 2 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 4
 - ③ TO ADJUST ROLLER DIRECTION, REMOVE ROLLER GUIDE LOCK RING, SCREW ROLLER GUIDE DOWN AS FAR AS POSSIBLE, THEN UNSCREW TO DESIRED DIRECTION. SECURE BY REPLACING ROLLER GUIDE LOCK RING
 - 4 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
 - 5 - CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
 - ⑥ HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[21EN239-R](#)