


THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.			THIRD ANGLE PROJECTION 		SCALE FULL		
CHARACTERISTICS		ELECTRICAL DATA				DO NOT SCALE PRINT	
OPERATING FORCE - - - - - 3-6 LB		CONTACT ARRANGEMENT				TOLERANCES	
FULL OVERTRAVEL FORCE - - - - - 17 LB MAX		SPNC (3)				APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±	
RELEASE FORCE - - - - - 2 LB MIN		LOAD		28 VDC		DIM. mm TOL. mm/in DIM. in TOL. mm/in	
PRETRAVEL - - - - - .040 MAX				NO PLACES ± .04 ONE PLACE ± .04 TWO PLACES ± .04 THREE PLACES ± .04 ANGLES ± .04			
DIFFERENTIAL TRAVEL - - - - - .020 MAX		SEA LEVEL		50,000 FT.		SI METRIC US CUSTOMARY	
OVERTRAVEL - - - - - .250 MIN		RES 7		7		DESIGN UNITS ☐ ☒	
		IND 4		2.5		RA* MATERIAL-COMMERCE STANDARD MICRO SWITCH STANDARDS APPLY	
		MOTOR 4				DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED	
						WEIGHT 6.0 OZ MAX	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[404EN53](#)