







WARNING- THIS PRODUCT IS SUBJECT TO THE U.S. INTERNATIONAL TRAFFIC IN ARMS REGULATIONS (ITAR), AND THE EXPORT CONTROL LAWS OF THE UNITED STATES. TRANSFER OF TECHNICAL DATA PERTAINING TO THIS PRODUCT BY ANY MEANS TO A FOREIGN PERSON PER ITAR DEFINITIONS. WHETHER IN THE UNITED STATES OR ABROAD, WITHOUT A PRIOR EXPORT LICENSE OR OTHER APPROVAL FROM THE U.S. DEPARTMENT OF STATE, IS PROHIBITED.

NOTES

- 1 - CORROSION RESISTANT STEEL ENCLOSURE
- 2 - SWITCH SEALED PER MIL-PRF-8805, SYMBOL 4
- ③ CIRCUIT DIAGRAM, CATALOG LISTING, AND DATE
- ④ CODE ARE SHOWN ON NAMEPLATE
- ④ HARDWARE MAY BE FURNISHED UNASSEMBLED PER MIL-PRF-8805
- 5 - TEMPERATURE: -67°F TO 260°F



D38999/25YA98PN
PER MIL-C-38999


ANSI Y14.5M-1982 APPLIES

[illegible]

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA		
OPERATING FORCE ----- 6 - 12 LBS		CONTACT ARRANGEMENT		
FULL OVERTRAVEL FORCE -- 30 LBS MAX		1 X S P D T		
RELEASE FORCE ----- 4 LBS MIN		LOAD (AMPS)	28 VDC	
PRETRAVEL ----- .040 MAX			SEA LEVEL	50,000 FT
DIFFERENTIAL TRAVEL -- .020 MAX		CONTACT	GOLD	GOLD
OVERTRAVEL ----- .125 MIN		RESISTIVE	1	1
		INDUCTIVE	.5	.5
		MOTOR		

THIRD ANGLE PROJECTION



SCALE **NONE**

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) $\pm .030$

TWO PLACE (.00) ±.015

THREE PLACE	(.000)	+ .005
-------------	--------	--------

THREE-EDGE 1.0007 ± 0.0005
ANGLES +

ANGLES	$\angle$
--------	----------

WEIGHT 4.5 OZ MAX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[622EN235-R](#)