




FO-52854  
DRAWN  
M J B 12 APR 72  
CHECK  
LSD  
19 APR 72  
CHECK  
JMG  
19 APR 72  
REVISIONS  
F 24 FEB 88 TSK CO62939 JAP 13 MAR 87 CEC 23 JAN 85 D CO-58417 JAS 4 FEB 85 C CO56672 B CO50565 GLH 20 JUN 73 A CO 32243  
REPLACES  
RELEASE NO. CO-30386  
DRAWING NUMBER  
7  
ISSUE  
X  
X  
X  
M12TWI-72 SERIES























**MICRO SWITCH**  
FREEPORT, ILLINOIS, U.S.A.  
A DIVISION OF HONEYWELL  
FED. MFG. CODE 91929


**SWITCH - TOGGLE**

CATALOG LISTING  
**12TWI-72 SERIES**  
**CHART 1**

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



CAT. LIST.	AVAILABLE LOCKING COMBINATIONS FOR CONFIGURATION SEE LETTERED DETAILS	STYLE NO.	ELECTRICAL DATA		MS NUMBER
			-L117-	5A-125 VAC 	
12TW1-72		1			MS27753-36
12TW1-72	E, L, N	2			MS27754-36 
"A"  LOCKED IN THREE POSITIONS	"B"  LOCKED IN CENTER AND EXTREME POSITION (KEYWAY SIDE)	"D"  LOCKED OUT OF CENTER POSITION	"E"  LOCKED IN CENTER POSITION	"F"  LOCKED IN EXTREME POSITION (OPPOSITE KEYWAY)	"G"  LOCKED IN EXTREME POSITION (KEYWAY SIDE)
"H"  LOCKED OUT OF CENTER AND EXTREME POSITION (KEYWAY SIDE)	"J"  LOCKED OUT OF CENTER AND EXTREME POSITION (OPPOSITE KEYWAY)	"K"  LOCKED IN CENTER AND EXTREME POSITION (OPPOSITE KEYWAY)	"L"  LOCKED OUT OF EXTREME POSITION (KEYWAY SIDE)	"M"  LOCKED OUT OF AND INTO EXTREME POSITION (OPPOSITE KEYWAY)	"N"  LOCKED OUT OF EXTREME POSITION (OPPOSITE KEYWAY)
"P"  LOCKED OUT OF AND INTO EXTREME POSITION (KEYWAY SIDE)	 LOCKWASHER (PART NO. TS-10013) 				
	 LOCKING RING (PART NO. EN-12449) 				
	 HEX NUT (2) (PART NO. TL-10632)  				



**NOTES**  
① FURNISHED UNASSEMBLED  
2 - TERMINALS ARE PLATED FOR SOLDERING  
③ MATTE FINISH  
④ SUFFIX LETTER MUST BE ADDED FOR DESIRED TYPE TOGGLE LOCKING. SEE CHART FOR AVAILABLE LOCKING COMBINATIONS.

SCALE 2 TO 1  
DO NOT SCALE PRINT  
UNLESS OTHERWISE NOTED  
DIMENSIONS ARE IN INCHES  
**TOLERANCES ARE:**  
ONE PLACE (.0) ±.030  
TWO PLACE (.00) ±.015  
THREE PLACE (.000) ±.005  
ANGLES  
WEIGHT

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Honeywell:

[12TW1-72](#) [12TW1-72E](#) [12TW1-72L](#) [12TW1-72N](#)