



REVISIONS	
A	CO 61252 MAM 18 MAR 87
B	CO62194 T S K 21 AUG 87
C	CO62939 T S K 24 FEB 88
D	CO- 95308 LJK 10 NOV 89

PTC/CAD	2D
DRAWN	LJK
CHECK	10NOV99
CHECK	JAF
CHECK	10NOV99

MICRO SWITCH
a Honeywell Division
FED. MFG. CODE 91929

SWITCH - TOGGLE

CATALOG LISTING
12TW1 SERIES
CHART 1



CATALOG LISTING	ONE EXTREME POSITION (KEYWAY)		CENTER POSITION		OTHER EXTREME POSITION (OPPOSITE KEYWAY)		MS NUMBER
	2-1	5-4	1-2	4-5	2-3	5-6	
12TW1-1	ON		OFF		ON		MS27719-21-1
12TW1-2	OFF		NONE		ON		MS27719-22-1
12TW1-3	ON		NONE		ON		MS27719-23-1
12TW1-5	MOM ON		OFF		ON		MS27719-31-1
12TW1-7	MOM ON		OFF		MOM ON		MS27719-27-1
12TW1-8	MOM ON		NONE		ON		MS27719-26-1
(D)	NONE		ON		ON		

NOTES
1 FURNISHED UNASSEMBLED
2 - TERMINALS ARE PLATED FOR SOLDERING

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH		THIRD ANGLE PROJECTION 	
CHARACTERISTICS	ELECTRICAL DATA		SCALE 2 : 1
	CONTACT ARRANGEMENT		DO NOT SCALE PRINT
	5A-125 VAC -L117- 		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±
			WEIGHT .025 LB MAX

ANSI Y14.5M-1982 APPLIES

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[MS27719-23-1](#)