




M12TWI-70 SERIES CHART 1
DRAWING NUMBER
ISSUE
REVISIONS
FO-52854
DRAWN
M J B
12 APR 72
CHECK
LSD
19 APR 77
CHECK
JW
17 APR 77
CHECK
JW
16 DEC 81
CHECK
JW
16 DEC 85
CHECK
JW
16 MAR 87
CHECK
JW
24 FEB 88
CHECK
JW

MICRO SWITCH
FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929


SWITCH - TOGGLE

CATALOG LISTING
12TWI-70 SERIES
CHART 1 ★

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



CAT. LIST.	AVAILABLE LOCKING COMBINATIONS FOR CONFIGURATION SEE LETTERED DETAILS	STYLE NO.	ELECTRICAL DATA		MS NUMBER
			-L117-	5A-125 VAC UL	
12TWI-70		1			MS27753-40
12TWI-70	E L N	2			MS27754-40 4
"A"		"B"		"D"	
"E"		"F"		"G"	
"H"		"J"		"K"	
"L"		"M"		"N"	
"P"					



NOTES
1 FURNISHED UNASSEMBLED
2 - TERMINALS ARE PLATED FOR SOLDERING
3 MATTE FINISH
4 SUFFIX LETTER MUST BE ADDED FOR DESIRED TYPE TOGGLE LOCKING. SEE CHART FOR AVAILABLE LOCKING COMBINATIONS.

SCALE 2 TO 1
DO NOT SCALE PRINT
UNLESS OTHERWISE NOTED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES
WEIGHT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[12TW1-70E](#) [12TW1-70N](#)