

M12TWI-10 SERIES

DRAWING NUMBER

27

ISSUE

33

REVISIONS

A PR 3999 12TWI-10 28 FEB 74

B CO 50565 TSK 15 DEC 81

C C056672 JAS 1 FEB 85

D C068417 JAW 1 MAR 87

E KEW 6 DEC 85

F C061252 TSK 24 FEB 88

FO-52854

DRAWN

MJB

12 APR 72

CHECK

10/11/82

RELEASE NO CO 30386

REPLACES




MICRO SWITCH
FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH - TOGGLE


CATALOG LISTING
12TWI-10 SERIES
CHART 1

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CAT. LIST.	AVAILABLE LOCKING COMBINATIONS FOR CONFIGURATION SEE LETTERED DETAILS	STYLE NO.	ELECTRICAL DATA		MS NUMBER
			-L117-	5A-125 VAC SP FL	
12TWI-10		1			MS27753-38
12TWI-10	ABDEFGHJKLMNP	2			MS27754-38



"A" 3 LOCKED IN THREE POSITIONS	"B" 3 LOCKED IN CENTER AND EXTREME POSITION (KEYWAY SIDE)	"D" 3 LOCKED OUT OF CENTER POSITION	"E" 3 LOCKED IN CENTER POSITION	"F" 3 LOCKED IN EXTREME POSITION (OPPOSITE KEYWAY)	"G" 3 LOCKED IN EXTREME POSITION (KEYWAY SIDE)
"H" 3 LOCKED OUT OF CENTER AND EXTREME POSITION (KEYWAY SIDE)	"J" 3 LOCKED OUT OF CENTER AND EXTREME POSITION (OPPOSITE KEYWAY)	"K" 3 LOCKED IN CENTER AND EXTREME POSITION (OPPOSITE KEYWAY)	"L" 3 LOCKED OUT OF EXTREME POSITION (KEYWAY SIDE)	"M" 3 LOCKED OUT OF AND INTO EXTREME POSITION (OPPOSITE KEYWAY)	"N" 3 LOCKED OUT OF EXTREME POSITION (OPPOSITE KEYWAY)
"P" 3 LOCKED OUT OF AND INTO EXTREME POSITION (KEYWAY SIDE)	.47 DIA .018 REF .60 DIA LOCKWASHER (PART NO. TS-10013) DIMENSIONS TO FIT KEYWAY IN BUSHING .05 .110 .392 .040 .72 DIA LOCKING RING (PART NO. EN-12449) 15/32-32 UNS-2 THREAD .078 .56 HEX NUT (2) (PART NO. TL-10632)				



NOTES
1 FURNISHED UNASSEMBLED
2 - TERMINALS ARE PLATED FOR SOLDERING
3 MATTE FINISH
4 SUFFIX LETTER MUST BE ADDED FOR DESIRED TYPE TOGGLE LOCKING. SEE CHART FOR AVAILABLE LOCKING COMBINATIONS.

SCALE 2 TO 1
DO NOT SCALE PRINT
UNLESS OTHERWISE NOTED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
ONE PLACE (.0)
TWO PLACE (.00)
THREE PLACE (.000)
ANGLES
WEIGHT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[12TW1-10](#) [12TW1-10A](#) [12TW1-10N](#) [12TW1-10P](#) [12TW1-10E](#)