

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

ASSEMBLY- PUSHBUTTON SWITCH

CATALOG LISTING

4PB714-T2

MILITARY P/N
M8805/23-003

4PB714-T2

PAGE 1 OF 1

M

DRAWING
NUMBER

ISSUE

9

REVISIONS

A PR-785

S R H
26 JUNE 69

B CO26314

S R H
4 SEPT 69

C CO27631

OMW
9 JUN 70

D CO27719

M B S
10 AUG 70

E CO32757

R E R
28 NOV 73

F CO-
93593

P P F
28 OCT 98

G CO-
94273

G J W
15 APR 99

H CO18511

S V
23 FEB 06

OMW

19 AUG 68

FORMTEK

0-30378-1A

DRAWN

OMW

19 AUG 68

REPLACES

RELEASE NO. PR785

28 OCT 98

J A F

CHECK

23 AUG 68

M G G

CHECK

23 AUG 68


L S D

CHECK

23 AUG 68

CHECK

19 AUG 68



NOTES

- 1- UNIT INCLUDES MS25085-2 TYPE BASIC SWITCH (4)
- 2- TERMINALS ARE PLATED FOR SOLDERING
- 3- SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
- △- MOUNTING HARDWARE FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE ----- 5.5 LB MAX

TOTAL TRAVEL ----- .100 APPROX

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T (4)

	SEA LEVEL			50,000 FT.
	28 VDC	115 VAC	28 VDC	
LOAD				
RESISTIVE	5	5	5	
INDUCTIVE	3	5	2.5	
LAMP	2.4	1.5	2.4	

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES ±

WEIGHT .075 LB MAX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[4PB714-T2](#)