

**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.  
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

**SWITCH-BASIC**

CATALOG LISTING

**DT-2R-A7**

MS 25008-1

L 0061834

T S K  
17 JUL 87**DT-2R-A7****M**DRAWING  
NUMBER

28

ISSUE

27

REPLACES

RELEASE NO.

CHECK

## REVISIONS

A CO17725

L E B  
27 MAY 83

B CO24941

M B S  
2 NOV 68

C CO26075

M B S  
26 AUG 69

D CO26678

R E R  
1 DEC 69

E CO37528

C J H  
31 AUG 76

F CO58589

R E R  
12 APR 77

G CO39046

G A S  
16 SEPT 77

H CO-50326

K A G  
24 NOV 81

J CO58827

T A D  
18 DEC 85

K CO62095

T S K  
10 JUL 87

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK


CHECK

CHECK

CHECK

CHECK

CHECK



## NOTE -

△ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS  
OF .139 MAX DIA ON  $1.000 \pm .002$  CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

**CHARACTERISTICS**

OPERATING FORCE ----- 12-20 OZ  
RELEASE FORCE ----- 2 OZ MIN  
DIFFERENTIAL TRAVEL ----- .040-.060  
OVERTRAVEL ----- .005 MIN

**ELECTRICAL DATA**

CONTACT ARRANGEMENT  
D P D T  
UNDERWRITERS' LAB. INC. LISTED RATING  
10 A-125 OR 250 VAC  
0.5 A-125 VDC; 0.15 A-250 VDC  
DWL

**SCALE FULL**

DO NOT SCALE PRINT

UNLESS OTHERWISE NOTED

DIMENSIONS ARE IN INCHES

**TOLERANCES ARE:**

ONE PLACE (.0)  $\pm .030$   
TWO PLACE (.00)  $\pm .015$   
THREE PLACE (.000)  $\pm .005$   
FOUR PLACE (.0000)  $\pm .001$

WEIGHT .078 LB MAX (D)

FO-80378

DRAWN

CHECK

CHECK

CHECK

CHECK

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[DT-2R-A7](#)