

DRAWING NUMBER  
**2TP12 SERIES CHART 1**

ISSUE  
**M**  
17

REVISIONS  
A CO-94413  
8 OCT 99  
B CO-195303  
C SL 15 NOV 99  
C 202714  
C SL 3 APR 01



RASTER  
FC-80378 003  
DRAWN  
H B W 18 SEP 64

RELEASE NO. SR 12719  
CHECK 22 SEP 64  
CHECK BRJ  
CHECK LSD  
REPLACES

**MICRO SWITCH**  
A DIVISION OF MINNEAPOLIS-MONFAYWELL REGULATOR CO  
FED. MFR CODE 91929

**SWITCH - TOGGLE  
FLUSH KEY**

CATALOG LISTING  
**2TP12 SERIES  
CHART 1**



CAT. LIST.	CIRCUIT MADE WITH BUTTON DEPRESSED ON		
	OPPOSITE LUG (2-3, 5-6)	CENTER (1-2, 4-5)	LUG SIDE (1-2, 4-5)
2TP12-1	ON	OFF	ON
2TP12-2	ON	NONE	OFF
2TP12-3	ON	NONE	ON
2TP12-21	ON	OFF	NONE
2TP12-4	ON	NONE	MOM OFF
ⓑ	ON	OFF	MOM ON
2TP12-6	OFF	NONE	MOM ON
2TP12-7	MOM ON	OFF	MOM ON
2TP12-8	ON	NONE	MOM ON
2TP12-61	NONE	OFF	MOM ON

L191 15A 125, 250, 277 VAC  
1/2HP 125 VAC  
1HP 250, 277 VAC  
5A 125 VAC "L"



L192 10A 125, 250, 277 VAC  
1/4HP 125 VAC,  
1/2HP 250, 277 VAC  
3A 125 VAC "L"



**NOTES**

- 1 - MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
- Ⓐ APPLIES ONLY TO "ON" AND "MOMENTARY ON" POSITIONS
- 3 - THESE SWITCHES WILL WITHSTAND TEMPERATURE OF 160°F
- Ⓐ SCREWS FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH A DIVISION OF MINNEAPOLIS-MONFAYWELL REGULATOR CO THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CHARACTERISTICS	ELECTRICAL DATA	SCALE - FULL
	CONTACT ARRANGEMENT	DO NOT SCALE PRINT
		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES <b>TOLERANCES ARE:</b> ONE PLACE ( ) ±.030 TWO PLACE (00) ±.015 THREE PLACE (000) ±.008 ANGLES ±
		WEIGHT .14 LB EST

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[2TP12-1](#) [2TP12-2](#) [2TP12-21](#) [2TP12-3](#) [2TP12-7](#) [2TP12-8](#)