

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
POMEROY, ILLINOIS

FED. MFR. CODE 91929

ASSEMBLY - TOGGLE SWITCH

CATALOG LISTING

23AT11-T2

23AT11-T2

M

DRAWING
NUMBER

ISSUE

3

4

REPLACES

RELEASE NO. SR 9300

CHECK

CHECK

CHECK

CHECK

CHECK


CHECK

CHECK

CHECK

CHECK

CHECK



- NOTE -**
- 1- UNIT INCLUDES CAT. LIST. ISM23-T2 BASIC SWITCH
 - 2- TERMINALS ARE PLATED FOR SOLDERING
 - 3- SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
 - 4- BASIC SWITCHES HAVE 24 K SOLID GOLD CONTACT MATERIAL

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

ELECTRICAL DATA

SCALE FULL

CONTACT ARRANGEMENT
S P D T (2)

DO NOT SCALE PRINT

30 VOLTS DC RATING

INDUCTIVE — — — — — SEA LEVEL — — 1/2 AMP
50,000 FT. — — 1/2 AMP
RESISTIVE — — — — — SEA LEVEL — — 1 AMP
50,000 FT. — — 1 AMP
MAXIMUM INRUSH — — — — — 2 AMP

UNLESS OTHERWISE
SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES ±

WEIGHT .06 LB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[23AT11-T2](#)