



REV	DOCUMENT	CHANGED BY	CHECK
11	0011406	KSR 23FEB05	AK

FAA-PMA LISTING 7	CATALOG LISTING	CIRCUIT MADE WITH TOGGLE LEVER IN			ELECTRICAL DATA .1A 30VDC (RESISTIVE)
		MICROPHONE SIDE 1 - 2	CENTER	INTERPHONE SIDE 2 - 3	
FAA-PMA	31TW2-207	MOM ON	OFF	MOM ON	
	31TW2-205	MOM ON	OFF	ON	
FAA-PMA	31TW2-62 5	MOM ON	OFF	NONE	



- NOTES
- 1 - TERMINATION WILL ACCEPT CRIMP CONTACTS CONFORMING TO M39029/1-101
 - 2 - ACTUATION TORQUE FOR MOMENTARY ACTION: 1.2 IN-LBS MAX
 - 3 - ACTUATION TORQUE FOR MAINTAINED ACTION: 1.5 IN-LBS MAX
 - 4 - TORQUES APPLY OVER A TEMPERATURE RANGE OF +5°F TO +140°F
 - 5 - SWITCHES MEET THE REQUIREMENTS OF MIL-S-83731 EXCEPT AS MODIFIED BY THIS DRAWING
 - 6 - TERMINAL NO.3 HOLE IS PLUGGED
 - 7 - SILVER CONTACTS
 - 8 - FOR MANUFACTURING DETAIL SEE THE CORRESPONDING ASSEMBLY DRAWING FOR EACH LISTING FOR FAA-PMA.

DESIGN UNITS: INCH		DRAWN	DLT	01JUL02	Honeywell				
TOLERANCES UNLESS NOTED:		CHECK	SAV	01JUL02					
NO PLACE	X	±	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.	TITLE					
ONE PLACE	.X	±		SWITCH,TOGGLE					
TWO PLACE	.XX	±							
THREE PLACE	.XXX	±							
FOUR PLACE	.XXXX	±	INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY	SIZE	TYPE	DRAWING NAME			REV
ANGLES	X	±	3°	C	I	31TW2 SERIES CHART 1			11
THIRD ANGLE PROJECTION			Pro/ENGINEER	2D	SCALE	3:1	WEIGHT .0625 LBS MAX	SHEET	1 OF 1
									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[31TW2-205](#) [31TW2-207](#) [31TW2-62](#)