

1TP8 SERIES

CHART 1

M

DRAWING NUMBER

15

ISSUE

RELEASE NO. PR-5907

REPLACES

REVISIONS

A	CO-51983
14	X AG SEP 82
B	CO56795
	J A P
27	MAR 85
C	CO57712
	T R F
14	NOV 85
D	CO59943
	J A P
23	JUL 86
E	CO77897
	T S M
15	JUN 94
F	CO94412
	D L M
13	OCT 99

FORMTEK

FO-52854-C

DRAWN

K A G

14 SEP 82

CHECK

14 SEP 82

14 SEP 82

MICRO SWITCH

FREEPORT ILLINOIS U S A

A DIVISION OF HONEYWELL

FED MFG CODE 51929


SWITCH - TOGGLE

FLUSH KEY

CATALOG LISTING

1TP8 SERIES

CHART 1



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.				
CATALOG LISTING	CIRCUIT MADE WITH BUTTON DEPRESSED ON			ELECTRICAL DATA
	LUG SIDE (1-2)	CENTER (1-2)	OPPOSITE LUG (2-3)	
1TP8 - 1	ON	OFF	ON	L191 15A 125, <u>250</u> , 277 VAC 1/2HP 125 VAC 1HP <u>250</u> , 277 VAC 5A 125 VAC "L"
1TP8 - 2	OFF	NONE	ON	
1TP8 - 3	ON	NONE	ON	
1TP8 - 21	NONE	OFF	ON	
1TP8 - 31	NONE	ON	ON	
1TP8 - 4	MOM OFF	NONE	ON	L192 10A 125, <u>250</u> , 277 VAC 1/4HP 125 VAC, 1/2HP <u>250</u> , 277 VAC 3A 125 VAC "L"
1TP8 - 5	MOM ON	OFF	ON	
1TP8 - 6	MOM ON	NONE	OFF	
1TP8 - 7	MOM ON	OFF	MOM ON	
1TP8 - 8	MOM ON	NONE	ON	
1TP8 - 51	NONE	ON	MOM ON	
1TP8 - 61	MOM ON	OFF	NONE	

- NOTES
- 1 - MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
 - 2 - THESE SWITCHES WILL WITHSTAND TEMPERATURE OF 160°F
 - 3 - SCREWS FURNISHED UNASSEMBLED

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED TOLERANCES ARE:

NO PLACES	DM	TOL	DM	TOL
ONE PLACE	mm	mm/in	in	mm/in
TWO PLACES	mm	0.13/0.005	in	0.005/0.13
THREE PLACES	mm	0.025/0.001	in	0.001/0.025

DESIGN UNITS

BI-METRIC

US CUSTOMARY

WEIGHT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Honeywell:

[1TP8-1](#) [1TP8-2](#) [1TP8-3](#) [1TP8-6](#) [1TP8-7](#) [1TP8-8](#) [1TP8-5](#)