




MICRO SWITCH
a Honeywell Division
FED. MFG. CODE 91929

ASSEMBLY-
TOGGLE SWITCH

CATALOG LISTING
64AT34 SERIES
CHART 1



4 CORROSION RESISTANT LEVER,
BUSHING AND BRACKET



- NOTES
- 1 - UNIT INCLUDES 4X 24K SOLID GOLD CONTACT "23SX" TYPE BASIC SWITCH (MEETS REQUIREMENTS OF MIL-PRF-8805)
 - 2 - SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
 - 3 - PLATED TERMINALS WILL ACCEPT AMPS INC Ø.058 PIN RECEPTACLES
 - 4 - DULL FINISH ON LEVER AND BUSHING
 - 5 - SWITCH NUMBERS STAMPED ON END OF BASIC SWITCHES
 - 6 - TERMINAL DESIGNATION STAMPED ON BOTH SIDES OF UNIT
 - 7 - 1-5 LB APPLIED .125 ± .030 TOP OF LEVER
 - 8 - HARDWARE FURNISHED ASSEMBLED WITH SWITCH OR IN PACKET 15PA313-AT PER MIL-PRF-8805
 - 9 - REPLACEMENT MOUNTING HARDWARE PACKET 15PA313-AT

DETAIL RATING CHART

VOLTS	CYCLE	INRUSH AMPERES		AMPERES SEA LEVEL				AMPERES 50,000 FT			
		NC	NO	RES	IND	MOTOR	LAMP	RES	IND	MOTOR	LAMP
30	DC	2	2	1	.5		.2	1	.5		.2
NOTE: INDUCTIVE LOADS: 30 VDC USE AN3179-6 INDUCTOR, 115 VAC AT 75% PF											
ANSI Y14.5M-1982 APPLIES											

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH	
CHARACTERISTICS	ELECTRICAL DATA
OPERATING FORCE ----- 7	CONTACT ARRANGEMENT 4X S P D T
DIFFERENTIAL FORCE	
RELEASE FORCE	
PRETRAVEL	
DIFFERENTIAL TRAVEL	
OVERTRAVEL	
FREE POSITION	

THIRD ANGLE PROJECTION	
SCALE	FULL
DO NOT SCALE PRINT	
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
ONE PLACE	(.0) ± .030
TWO PLACE	(.00) ± .015
THREE PLACE	(.000) ± .005
ANGLES	±
WEIGHT	.07 LB EST

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[64AT34-3](#) [64AT34-7](#)