

DRAWN								PAGE 1 OF 1			REF. ACES X78435-TW				
M	I DEC 83	CHECK	E.	S	CEC	3	TAE	00	074	K 88	939	P 86	NS 236	4	H LEASE NO. PR-12333

MICRO SWITCH
FREEPORT ILLINOIS U S A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-TOGGLE

CATALOG LISTING
1TW101 SERIES
CHART 1

CATALOG
LISTING


CIRCUIT MADE WITH TOGGLE LEVER IN		
TAB SIDE (1-2)	CENTER (1-2)	OPPOSITE TAB (2-3)

ELECTRICAL RATING

5A - 125 VAC

5A - 125 VAC

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.




	CATALOG LISTING	CIRCUIT MADE WITH TOGGLE LEVER IN		
		TAB SIDE (1-2)	CENTER (1-2)	OPPOSITE TAB (2-3)
	ITWIOI - 1	ON	OFF	ON
	ITWIOI - 2	OFF	NONE	ON
	ITWIOI - 3	ON	NONE	ON
	ITWIOI - 2I	NONE	OFF	ON
	ITWIOI - 3I	NONE	ON	ON
	ITWIOI - 4	MOM OFF	NONE	ON
	ITWIOI - 5	MOM ON	OFF	ON
	ITWIOI - 6	MOM ON	NONE	OFF
	ITWIOI - 7	MOM ON	OFF	MOM ON
	ITWIOI - 8	MOM ON	NONE	ON
	ITWIOI - 5I	NONE	ON	MOM ON
	ITWIOI - 6I	MOM ON	OFF	NONE

NOTES

① FURNISHED UNASSEMBLED

② - TERMINALS ARE COATED FOR SOLDERING

③ MATTE FINISH



SCALE 2:1		
DO NOT SCALE PRINT		
UNLESS OTHERWISE NOTED		
DIMENSIONS ARE IN INCHES		
TOLERANCES ARE:		
ONE PLACE	(.01)	± .030
TWO PLACE	(.00)	± .015
THREE PLACE	(.000)	± .005
ANGLES		
WEIGHT .025 LB MAX		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Honeywell:

[1TW101-3](#) [1TW101-7](#) [1TW101-8](#) [1TW101-2](#)