

# MICRO SWITCH

FREEPORT ILLINOIS, U.S.A  
A DIVISION OF HONEYWELL  
FED. MFG. CODE 91929

## ASSEMBLY- TOGGLE SWITCH

CATALOG LISTING  
**13AT10-T2-B**

CATALOG LISTING  
**13AT10-T2-B**

**M**

DRAWING  
NUMBER

ISSUE

### REVISIONS

A	CO	39476
22	GLH	NOV 77
B	CO	50566-B
5	WJM	MAY 82
C	CO-52725	
2	KAG	JUN 83
D	CO-66089	
13	DAW	FEB 91
E	CO92636	
17	GJW	DEC 98
F	207108	
	CSL	JAN 03

RASTER

FO-52848-A

DRAWN

REPLACES

RELEASE NO. PR-5082


CHECK

CHECK

12 JUN 75

12 JUN 75

12 JUN 75




### NOTES

- 1 - UNIT INCLUDES CATALOG LISTING 1SM1-T2 TYPE BASIC SWITCH (4)
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - HARDWARE FURNISHED ASSEMBLED WITH SWITCH OR IN PACKET PER MIL-PRF-8805
- 4 - REPLACEMENT MOUNTING PACKET 15PA312-AT

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



### CHARACTERISTICS

### ELECTRICAL DATA

SCALE FULL

CONTACT ARRANGEMENT  
S P D T (4)

DO NOT SCALE PRINT

250 VAC ----- 5 AMP  
30 VOLTS DC RATING  
INDUCTIVE ----- SEA LEVEL --- 3 AMP  
50,000 FT --- 2.5 AMP  
RESISTIVE ----- SEA LEVEL --- 5 AMP  
50,000 FT --- 5 AMP  
MAXIMUM INRUSH ----- 24 AMP

TOLERANCES			
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±			
DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/64	X X
ONE PLACE	X, X	0.4/0.16	X X X
TWO PLACES	X, XX	0.15/0.006	X, XX X
THREE PLACES	X, XXX		
ANGLES			
SI METRIC		US CUSTOMARY	
DESIGN UNITS			

WEIGHT

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[13AT10-T2-B](#)