



REVISIONS	
A	CORR
B	DBW 18 JUN 73
C	PR-4606
D	CO50565
E	CJH 16 DEC 81
F	CO61252
G	JAP 13 MAR 87
H	CO61838
I	TSK 22 JUL 87
J	CO62939
K	TSK 24 FEB 88
L	CO-93153
M	JJA 13 MAY 99


H
MICRO SWITCH
FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH - TOGGLE

CATALOG LISTING
12TW8 SERIES
CHART 1



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.		
CHARACTERISTICS	ELECTRICAL DATA	SCALE 2 TO 1
	CONTACT ARRANGEMENT	DO NOT SCALE PRINT
	-L117- 5A-125 VAC	UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES TOLERANCES ARE: ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±
		WEIGHT .025 LB MAX



CATALOG LISTING	CIRCUIT WITH TOGGLE IN			
	ONE EXTREME POSITION (KEYWAY)		CENTER POSITION	OTHER EXTREME POSITION (OPPOSITE KEYWAY)
	2-1	5-4		2-3 5-6
12TW8-1	ON		OFF	ON
12TW8-2	OFF		NONE	ON
12TW8-3	ON		NONE	ON
(G)	MOM ON		OFF	ON
12TW8-7	MOM ON		OFF	MOM ON
12TW8-8	MOM ON		NONE	ON

NOTE -
1 - FURNISHED UNASSEMBLED
2 - TERMINALS ARE PLATED FOR SOLDERING
3 - MATTE FINISH
4 - GOLD PLATED CONTACTS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Honeywell:

[12TW8-7](#) [12TW8-1](#) [12TW8-3](#) [12TW8-8](#)