

**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ - 2RD - P1**AHD3000****BZ - 2RD - P1**

PAGE 1 OF 1

MDRAWING
NUMBERISSUE
10

REPLACES

RELEASE NO.

CHECK

17 FEB 06

RJ

CHECK

14 JUN 63

CHECK

L.S.D.

22 APRIL 63

G C H

REVISIONS

A CO17410

S C H
22 APRIL 63

B CO31863

S R H
27 MAR 73


C CO 58037

S M A
1 OCT 85D CO-
73287-GJ A L
20 OCT 93E CO-
77591D A W
22 JUN 94

F CO93346

D L T
1 SEP 98G CO-
94212-CD L T
14 SEP 99

H 0018448

D V M
17 FEB 06

NOTE

△ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON $1.000 \pm .002$ CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE ----- 9 - 13 OZ

RELEASE FORCE ----- 4 OZ MIN

DIFFERENTIAL TRAVEL ----- .0004 - .0020

OVERTRAVEL ----- .060 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

15A - 125, 250 OR 480 VAC, 2A - 600 VAC
-L74- 1/8HP - 125 VAC; 1/4HP - 250 VAC
1/2A - 125 VDC; 1/4A - 250 VDC

-L288-
-L315-
-L306-



16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) $\pm .030$
TWO PLACE (.00) $\pm .015$
THREE PLACE (.000) $\pm .005$
ANGLES \pm

WEIGHT .076 LB

FORMTEK

FO-50378

DRAWN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZ-2RD-P1](#)