



HONEYWELL
PART NUMBER
1TP1 SERIES CHART 1

REV	DOCUMENT	CHANGED BY	CHECK
7	0007019	KR 12AUG04	AK



- NOTES
- 1 - MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
 - 2 - SWITCHES WILL WITHSTAND TEMPERATURE OF 160°F
 - 3 - SCREWS FURNISHED UNASSEMBLED
 - 4 - FAA-PMA MUST BE MARKED ON SWITCH
 - 6 - FOR MANUFACTURING DETAIL SEE ASSEMBLY DRAWING 1TP1-2 FOR FAA-PMA
 - 6 - WEIGHT: .10 LB EST

4	CATALOG LISTING	CIRCUIT WITH BUTTON IN			ELECTRICAL DATA
		LUG SIDE (1-2)	CENTER (1-2)	OPPOSITE LUG (2-3)	
FAA-PMA	1TP1-1	ON	OFF	ON	15A-125, 250 OR 277 VAC 1/2HP-125VAC; 1HP-250, 277VAC 5A-125VAC "L" CODE L191
	1TP1-2	OFF	NONE	ON	
	1TP1-3	ON	NONE	ON	
	1TP1-2I	NONE	OFF	ON	
	1TP1-3I	NONE	ON	ON	
	6	MOM OFF	NONE	ON	10A-125, 250, 277 VAC 1/4HP-125VAC; 1/2HP-250, 277 VAC 3A-125VAC "L" CODE L192
	1TP1-5	MOM ON	OFF	ON	
	1TP1-6	MOM ON	NONE	OFF	
	1TP1-7	MOM ON	OFF	MOM ON	
	1TP1-8	MOM ON	NONE	ON	
	6	NONE	ON	MOM ON	
	1TP1-6I	MOM ON	OFF	NONE	

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:

NO PLACE	X	±	
ONE PLACE	.X	±	0.030
TWO PLACE	.XX	±	0.015
THREE PLACE	.XXX	±	0.005
FOUR PLACE	.XXXX	±	
ANGLES		±	

THIRD ANGLE PROJECTION

DRAWN	GJW	12MAY97
CHECK		
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

REPLACES 1TP1 SERIES			
Honeywell			
TITLE SWITCH - TOGGLE FLUSH KEY			
SIZE	TYPE	DRAWING NAME	REV
B	I	1TP1 SERIES CHART 1	7
SCALE	1:1	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Honeywell:

[1TP1-1](#) [1TP1-2](#) [1TP1-3](#) [1TP1-31](#) [1TP1-5](#) [1TP1-6](#) [1TP1-7](#) [1TP1-8](#)